





FED. MFG. CODE 91929

CATALOG LISTING
404HE99-6

CATALOG LISTING



CIRCUIT DIAGRAM




1 - CORROSION RESISTANT STEEL ENCLOSURE
2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 5
3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 INCH
OF PLUNGER TRAVEL
5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA		T SCALE FULL	
OPERATING FORCE — — — — 6 —12 LB		CONTACT ARRANGEMENT 4X S P D T		DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE --- 30 LB MAX			28 VDC	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.03 TWO PLACE (.00) ±.01 THREE PLACE (.000) ±.001 ANGLES ±	
RELEASE FORCE — — — — — 4 LB MIN		LOAD	SEA LEVEL AND 100,000 FT		
PRETRAVEL — — — — — .040 MAX		RES	7		
DIFFERENTIAL TRAVEL — — — — — .020 MAX		IND	4		
OVERTRAVEL — — — — — .250 MIN		MOTOR	4		
				WE I G H T	

THIRD ANGLE PROJECTION



SCALE	FULL
-------	------

DO NOT SCALE PRINT

**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE**

ONE PLACE (.0) $\pm .030$

TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005

THREE PLACE	(.000)	1.000
ANGLES		+

WEIGHT

ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[404HE99-6](#)