




- 1 OPERATION TEMPERATURE IS 105° C MAX.
- 2 RETENTION FORCE — 16 OUNCES MIN INITIALLY.
6 OUNCES MIN AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN.
- 4 .175 MAX TO BE MEASURED ACROSS THE CUT-OFF TABS.

	NYLON 6/6; WHITE	BRASS – GOLD	3-582118-9
OBSOLETE	NYLON 6/6; GRAY	BRASS – GOLD	3-582118-8
	NYLON 6/6; VIOLET	BRASS – GOLD	3-582118-7
	NYLON 6/6; BLUE	BRASS – GOLD	3-582118-6
	NYLON 6/6; GREEN	BRASS – GOLD	3-582118-5
	NYLON 6/6; YELLOW	BRASS – GOLD	3-582118-4
	NYLON 6/6; ORANGE	BRASS – GOLD	3-582118-3
	NYLON 6/6; RED	BRASS – GOLD	3-582118-2
OBSOLETE	NYLON 6/6; BROWN	BRASS – GOLD	3-582118-1
	NYLON 6/6; BLACK	BRASS – GOLD	3-582118-0
	NYLON 6/6; WHITE	BRASS – SILVER	2-582118-9
OBSOLETE	NYLON 6/6; GRAY	BRASS – SILVER	2-582118-8
OBSOLETE	NYLON 6/6; VIOLET	BRASS – SILVER	2-582118-7
	NYLON 6/6; BLUE	BRASS – SILVER	2-582118-6
OBSOLETE	NYLON 6/6; GREEN	BRASS – SILVER	2-582118-5
OBSOLETE	NYLON 6/6; YELLOW	BRASS – SILVER	2-582118-4
OBSOLETE	NYLON 6/6; ORANGE	BRASS – SILVER	2-582118-3
	NYLON 6/6; RED	BRASS – SILVER	2-582118-2
OBSOLETE	NYLON 6/6; BROWN	BRASS – SILVER	2-582118-1
	NYLON 6/6; BLACK	BRASS – SILVER	2-582118-0
	NYLON 6/6; WHITE	BRASS – TIN	1-582118-9
OBSOLETE	NYLON 6/6; GRAY	BRASS – TIN	1-582118-8
OBSOLETE	NYLON 6/6; VIOLET	BRASS – TIN	1-582118-7
OBSOLETE	NYLON 6/6; BLUE	BRASS – TIN	1-582118-6
	NYLON 6/6; GREEN	BRASS – TIN	1-582118-5
	NYLON 6/6; YELLOW	BRASS – TIN	1-582118-4
OBSOLETE	NYLON 6/6; ORANGE	BRASS – TIN	1-582118-3
	NYLON 6/6; RED	BRASS – TIN	1-582118-2
OBSOLETE	NYLON 6/6; BROWN	BRASS – TIN	1-582118-1
	NYLON 6/6; BLACK	BRASS – TIN	1-582118-0

	—	—	—
	—	—	—
	—	—	—
	NYLON 6/6; NATURAL	BRASS — GOLD	6-582118-9
OBSOLETE	NYLON 6/6; NATURAL	BRASS — SILVER	5-582118-9
	HOUSING — MATERIAL; COLOR	RECEPTACLE — MATERIAL; FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER		13APR2004		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK E. HOWARD		13APR2004			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E. HOWARD		NAME ASSEMBLY, TEST PROBE	
				PRODUCT SPEC —		—	
				APPLICATION SPEC —		—	
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
SEE TABLE		SEE TABLE		—		—	
CUSTOMER DRAWING						SCALE 6:1 SHEET 1 OF 1 REV AR	