



AMP WIRE RANGE	 E13288 Listed
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED


 LR7189 Certified	MILITARY P/N AND CLASS
16-14 AWG SOLID OR STRANDED	NOT APPLICABLE

- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2


MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS
- 3

P/N 8-31819-6 IS NOT UL/CSA APPROVED.



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm ² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

5 PCS/BAG	LOOSE PIECE, BAG	3 8-31819-6
50	LOOSE PIECE, BAG	8-31819-5
100	LOOSE PIECE, BOX	8-31819-1
2500	ON TAPE	2-31819-1
----	LOOSE PIECE	31819
QUANTITY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-13-93	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 4-13-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DE MILLER 4-13-93	NAME	
		PRODUCT SPEC	SPLICE, BUTT, STANDARD, SOLISTRAND	
MATERIAL		APPLICATION SPEC	SIZE	
COPPER PER ASTM B-152 ANNEALED		FINISH	CAGE CODE	
TIN PLATE 0.0025[.000100] MIN THK PER MIL-1-10727		WEIGHT	DRAWING NO	
			RESTRICTED TO	
			A2 00779 C-31819	
			CUSTOMER DRAWING	
			SCALE 10:1	
			SHEET 1 of 1	
			REV J1	