



30A 125/250V
NEMA L14-30R
UL/CSA
2 (2) HP



30A 3Ø 250V AC
NEMA L15-30R
UL/CSA
3 HP

Connector Bodies

Watertight Safety-Shroud®

IP66 SUITABILITY

Description	Cord Dia.	Catalog Numbers	
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	HBL2713SW	HBL2723SW

Insulgrip

IP20 SUITABILITY

Description	Cord Dia.	Catalog Numbers	
Black and white nylon.	.35"-1.15" (9-29)	HBL2713	HBL2723
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	HBL27CM13	HBL27CM23
All black nylon.	.35"-1.15" (9-29)	HBL2713BK	-

Accessories on page B-53.



HBL2713SW



HBL2713

Receptacles

Watertight Safety-Shroud, Back Wired

IP66 SUITABILITY

Description	Catalog Numbers	
Gray Valox® housing and flange.	HBL2710SW	HBL2720SW

Accessories on page B-54.

Safety-Shroud Twist-Lock, Back Wired

IP20 SUITABILITY

Description	Catalog Numbers	
Gray Valox® angle housing, one gang.	HBL2710AR	HBL2720AR
Gray Valox® surface mounting, one gang.	HBL2710SR	HBL2720SR
Gray Valox® semi-flush, two gang.	HBL2710SR2	HBL2720SR2

Accessories on page B-54.



HBL2710SW

Single Flush, Back and Side Wired

IP20 SUITABILITY

Description	Catalog Numbers	
Black nylon face.	HBL2710	HBL2720
Isolated ground, orange nylon face.	IG2710	IG2720
Ring terminal connection.	HBL2710RT	HBL2720RT

Accessories on page B-52.




HBL2710AR


Insulgrip Flanged Receptacles

Description	Catalog Numbers	
Nylon casing, back wired.	HBL2716	HBL2726


Accessories on page B-52.



HBL2716



HBL2710



HBL2710SR2



HBL2710SR

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.