



PART NAME	POTTING BOX COVER					PART No.	PBC-1558-C PBC-1576-CN		PBC-1574-CN PBC-1577-CN		REV. DATE	9-22-10		
MATERIAL: ABS THERMOPLASTIC (CHI MEI POLYLAC PA-765) (FLAMMABILITY RATING OF 94V-0 AT "M" INCHES THICKNESS & CONTINUOUS USE TEMPERATURE OF 70° C.) FINISH: SURFACES ARE SMOOTH. COLOR: BLACK COVER REDUCES INSIDE HEIGHT OF BOX BY "N" INCHES. 														
PART No.	A	B	C	D	E	F	G	H	J	K	L	M	N	FITS BOX:
PBC-1558-C	2.000	1.738	1.500	1.238	0.063	0.085	0.614	0.500	0.063	0.163	0.062	0.063	0.100	PB-1558-BF
PBC-1574-CN	2.000	1.750	2.000	1.750	0.060	0.077	0.812	0.515	0.062	0.156	0.066	0.070	0.094	PB-1574-BF
PBC-1576-CN	3.000	2.735	3.000	2.735	0.070	0.082	1.310	0.500	0.062	0.156	0.066	0.070	0.094	PB-1549, 76-BF
PBC-1577-CN	1.000	0.828	1.000	0.828	0.050	0.050	0.368	0.187	0.068	0.146	0.051	0.070	0.078	PB-1577-BF

PART NAME	POTTING BOX COVER				PART No.	PBC-1558-CN PBC-1574-C TO PBC-1576-C PBC-1578-C TO PBC-1580-C				REV. DATE	8-28-06
MATERIAL: ABS THERMOPLASTIC (CHI MEI POLYLAC PA-765) (FLAMMABILITY RATING OF 94V-0 AT "G" INCHES THICKNESS & CONTINUOUS USE TEMPERATURE OF 70° C.) FINISH: SURFACES ARE SMOOTH. COLOR: BLACK COVER REDUCES INSIDE HEIGHT OF BOX BY "H" INCHES.											
PART No.	A	B	C	D	E	F	G	H	FITS BOX:		
PBC-1558-CN	1.982	1.482	0.075	0.270	0.080	0.250	0.063	0.075	PB-1558, PB-1558-TF		
PBC-1574-C	2.000	2.000	0.075	0.270	0.080	0.250	0.063	0.075	PB-1574, PB-1574-TF		
PBC-1575-C	3.000	2.000	0.075	0.270	0.080	0.250	0.063	0.075	PB-1559, PB-1559-TF, PB-1575, PB-1575-TF		
PBC-1576-C	3.000	3.000	0.075	0.270	0.080	0.250	0.063	0.075	PB-1576, PB-1576-TF		
PBC-1578-C	2.160	4.030	0.085	0.287	0.109	0.278	0.070	0.085	PB-1578, PB-1578-TF, PB-1582, PB-1582-TF		
PBC-1579-C	1.472	1.222	0.075	0.270	0.080	0.250	0.063	0.075	PB-1579, PB-1579-TF		
PBC-1580-C	4.000	1.750	0.075	0.270	0.080	0.250	0.063	0.075	PB-1580, PB-1580-TF		

PART NAME	POTTING BOX COVER				PART No.	PBC-1577-C	PBC-1581-C	PBC-1583-C	REV. DATE	8-28-06
MATERIAL: ABS THERMOPLASTIC (CHI MEI POLYLAC PA-765) (FLAMMABILITY RATING OF 94V-0 AT "H" INCHES THICKNESS & CONTINUOUS USE TEMPERATURE OF 70° C.) FINISH: SURFACES ARE SMOOTH. COLOR: BLACK COVER REDUCES INSIDE HEIGHT OF BOX BY "J" INCHES.										
PART No.	A	B	C	D	E	F	G	H	J	FITS BOX:
PBC-1577-C	1.010	1.010	0.060	0.250	0.060	0.185	0.030	0.060	0.060	PB-1577, PB-1577-TF
PBC-1581-C	1.222	2.019	0.075	0.218	0.070	0.130	0.035	0.070	0.075	PB-1581, PB-1581-TF
PBC-1583-C	3.118	4.373	0.100	0.350	0.095	0.250	0.052	0.070	0.110	PB-1583, PB-1583-TF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bud Industries:

[PBC-1576-CN](#) [PBC-1583-C](#) [PBC-1558-CN](#) [PBC-1558-C](#) [PBC-1574-CN](#) [PBC-1580-C](#) [PBC-1574-C](#) [PBC-1579-C](#)
[PBC-1559-C](#) [PBC-1575-C](#) [PBC-1578-C](#) [PBC-1577-C](#) [PBC-1577-CN](#) [PBC-1581-C](#) [PBC-1576-C](#)