



SFP+ PLUGGABLE I/O INTERCONNECTS

Quick Reference Guide

TE Connectivity's (TE) family of SFP+ interconnects are designed to transfer data at speeds of up to 16 Gb/s. The portfolio features 20-position SMT connectors as well as cages in multiple configurations, and with elastomeric gasket or enhanced EMI springs to address EMI containment at higher data rates. The SFP+ interconnect family also includes thermal- and EMI-enhanced stacked configurations to further improve performance.

Complementary SFP+ direct-attach copper cable assemblies are also offered by TE as a high-speed, cost-effective alternative to fiber optic cables. These assemblies enable hardware OEMs and data center operators to achieve high port density and configurability at low costs and with reduced power requirements.

FEATURES AND BENEFITS

Interconnect

- Supports applications up to 16 Gb/s
- Cages available in single-port, ganged and stacked configurations. Belly-to-belly mounting cages also offered.
- Uses enhanced 20-position connector that is backward-compatible with SFP connectors
- Features elastomeric gaskets and springs for EMI containment
- Offers heat sink and light pipe options

Direct-Attach Copper Cable Assemblies

- Complies to SFF-8431 specifications
- Supports up to 10 Gb/s serial data rates
- Serves as a low-cost alternative to fiber optic cables
- Consumes low power
- Offers enhanced EMI suppression
- Features a pull-to-release retractable pin latch

te.com/products/sfpplus

SFP+ Pluggable I/O Interconnects


Product Applications

- Storage, servers, routers, switches and hubs
- Network Interface Cards (NICs)
- Other telecommunications equipment

Applications by Protocol

- 10 Gigabit Ethernet (IEEE802.3ae)
- Fibre Channel: 2G, 4G, 8G and 16G
- Fibre Channel over Ethernet (FCoE)

SFP+ Thermal and EMI Enhancements



Thermal Enhancements


SFP+ stacked cages have been modified to enhance thermal performance. These changes include revised side walls of the cage for airflow through the middle of the cage to promote cooling of lower ports

Additionally, two thermal vent holes have been added to each port to further enhance thermal performance.

EMI Enhancements

SFP+ stacked cages with EMI enhancements feature a gasket retention plate with multiple attachment points that improve the electrical connection to the cage. A new right-angle design of the gasket retention plate also improves the strength of the product.

A pocket spring has been added to the latch plate area to further reduce EMI emission. This component is internal to the cage assembly. The additional component still allows airflow through the front of the cage assembly.



Configuration	Part Number	Cage Design
Single Port	2007198-1	11-Pin Press-Fit (PF)
	2110304-1	Standard Solder Tail
	2007194-1	PCI Solder Tail
	2057086-2	Enhanced Footprint
1x2	2007263-1	PF, Thermal Vent Holes
1x4	2169260-1	Heat Sink Slots
1x5	2284170-1	Heat Sink Slots
1x6	2007251-1	PF, Thermal Vent Holes

Configuration	Part Number	Cage Design
2x1	2007538-X	Elastomeric Gasket
2x1	2170409-X	Thermally-Enhanced
2x2	2007637-X	EMI Spring Version
2x4	2007399-X	Elastomeric Gasket
2x4	2274010-X	Thermally-Enhanced
2x6	2007562-X	EMI Spring Version
2x6	2180640-X	Thermally-Enhanced
2x8	2149490-X	EMI Spring Version

To see more part numbers, visit www.te.com/products/sfpplus or refer to the Pluggable Input/Output Solutions Catalog 1773408-1

SFP+ Pluggable I/O Interconnects

20 Pin SMT Connector	
PN	Description
2110759-1	Rated to 16G
1888247-1	30 µin Au
1888247-2	15 µin Au

Dust Cap	
PN	Description
1367147-X	Dust Cap
1888901-1	EMI Plug
1761394-1	Dust Cap (narrow for multiport cages)

Cable Assembly Features and Benefits

- Truly broadband - operates from 1 to 10 Gb/s
- 100 Ohm differential impedance
- 3.3 V input source voltages
- Pull tab allows compact belly-to-belly application
- 360 degree cable braid crimp and enhanced EMI skirt
- Uses MADISON CABLE brand TurboTwin parallel pair cable

Direct Attach Copper Cable Assemblies																		
PN	Description	AWG	Cable Length (meters)															
			0.5	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
2127934	Standard Passive	24	-1	-2	-3	-4	-5	-6	-7	-8								
2127933	Other Passive	26	-1	-2	-3	-4	-5	-6	-7									
2127932		28	-1	-2	-3	-4	-5	-6										
2127931		30	-1	-2	-3	-4												
2032757	Active	24												-12	-13	-14	-15	-16
		28										-10	-11					
		30	-1	-2	-3	-4	-5	-6	-7	-8	-9							
2053453	SFP+ to QSFP+ Hybrid	26						-6										
		28					-5											
		30	-1	-2	-3	-4												

Frequently Asked Questions

What is belly-to-belly mounting?

- Belly-to-belly mounting allows a customer to install connectors and cages on both sides of a PCB. This design reduces board space and is an alternative solution to stacked connectors.

If I am currently using SFP cabling, can I use SFP+ host board configurations?

- Yes. SFP+ configurations support higher rates. You can design SFP+ products in the host board for future upgrades.

What data rate does SFP support?

- SFP supports up to 16Gb/s.

What are the PCB termination options?

- Cages are offered in press-fit and solder PCB termination styles.

Is TE's footprint compatible with other suppliers?

- It depends. The single port cages are designed to industry standards. The ganged versions are not compatible with all other sources.

Are heat sinks available?

- Yes. Riding heat sink technology is available for thermal management.

Is application tooling required?

- Single port assemblies do not require application tooling, yet ganged assemblies do require application tooling.

For More Information

te.com/products/sfpplus

TE Technical Support Center

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved.

4-1773455-3 DND PDF 02/2017

MADISON CABLE, TurboTwin, TE Connectivity, TE and TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other logos, product and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.