






DETAIL A  
SCALE 30/1




COPLANARITY : 0 Max / -0.1 mm Min  
Reference plan ; bearing surface of housing



COUPE B-B



Contact numbering




NOTES:





Housing material : High temperature thermoplastic, dark grey colour  
Terminal material : Phosphor bronze  
Plating : Nickel all over followed by min 0.8u Au on contact area  
Tin-Lead ( SnPb 60/40 or 90/10 ) on solder area, Bare edge allowed  
Tape and reel packaging  
Contact force : 0.2 - 0.8N

CUSTOMER PART NUMBER : 5409201  
FCI PART NUMBER : MNA04ECE01

LAYOUT PROPOSAL



rev	ecn no	dr	date
G	LS2059	-	2002/05/23
H	106-0084	SSC	2006/06/21
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface -- 		tolerance std		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	LE GALLIC	2001/06/27	ANGULAR	LINEAR	0.x	±	size	A2	Scale	S/I
Eng	--	--			0.xx	±				
Chr	DILIP THOMAS	2006/06/21			0.xxx	±				
Appr	K.V.SIVADAS	2006/06/21	Product family		MOBILE I/O		Spec ref		106-0084	
			title				SIM CONNECTOR		Re	
			TYPE S16				CO1MNA04ECE01		H	
			catalog no				MNA04ECE01		CUSTOMER	
									sheet 1 of	