

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301100034

Status:

Active

Overview:

Wide-Area Lighting Products

Description:

Wet Location 70W Metal Halide Magnet Mount Area Light with Feed Thru, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E174254
General	
Product Family	Portable Lighting
Series	130110
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 3
Outlet	Feed-Through
Overview	Wide-Area Lighting Products
Product Name	Woodhead
Type	Wide Area Lamps
UPC	78678829572
Physical	
Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	0.305m (1.0')
Depth	207.26mm (8.160")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	264.16mm (10.400")
Length	228.60mm (9.000")
Material - Globe	Clear Polycarbonate
Material - Guard	N/A
Mounting Style	Magnet
Net Weight	5597.325/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Metal Halide - Probe Start
Cord Type - Primary	16/3 SJTOW
Cord Type - Secondary	16/3 SJTOW
Lamp Type	MH70
Lamp Wattage - Maximum	70W
Lumens	3600
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	8565F-MH

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130110 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION