



English | 简体中文 | 日本語

Search by Part Number



Search Site by keyword



Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > Clock / Timing Devices > PC-Notebook-Server Clocks > DDR I and DDR II Buffers > Zero Delay Buffers > 9P946 > 9P946AFLFT

You may also like...

9P946AFLFT

Category: Zero Delay Buffers
Generic Part: 9P946
Market Group: PC CLOCK
Description: PC BUFFER
Dual DDR zero delay buffer

Product Description/Features:

- High performance, low jitter zero delay buffer
- I2C for functional and output control
- Dual bank 1-6 differential clock distribution
- 2 separate feedback in & out for input to output synchronization for each bank
- Supports up to 4 DDR DIMMs
- Supports up to 533MHz (DDRII 1066)



Parameters

Temperature	C
Voltage	3.3 V
Package	SSOP48
Speed	NA
Status	Active
Sample	No
Minimum Order Quantity	1000
Factory Order Increment	1000

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Package	SSOP48 (PVG48)
Description	SSOP300 MIL
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	F
Package Type	SSOP
Lead Count	48
Length	15.9 mm
Width	7.5 mm
Thickness	2.3 mm
Pitch	0.64 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	30
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85% RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	NA
Related Package Documents	view documents