




(1,27 mm) .050"



TFSD, TFSDT SERIES

TIGER EYE™ DISCRETE CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications see www.samtec.com?TFSD or www.samtec.com?TFSDT

Insulator Material:

Black LCP

Contact Material:

BeCu

Plating:

Au over 50μ" (1,27 μm) Ni

Operating Temp Range:

-10°C to +80°C (PVC)

-40°C to +125°C (*Teflon®)

Wire:

28 or 30 AWG

RoHS Compliant:

Yes

Mates with:

SFM, SFC (-TR requires

TFM-WT option),

SFML (-XL end option

required)

Single or
Double
Ended

28 or 30
AWG

(1,27 mm)
.050"
pitch

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

TYPE STRIP

TFSD
= Double Row PVC Cable

TFSDT
= Double Row *Teflon® Cable

POSITIONS PER ROW

-03, -04,
-05, -07,
-10, -15,
-20, -25,
-40, -50
(Standard sizes)

WIRE GAUGE

-30
= 30 AWG
-28
= 28 AWG

PLATING OPTION

-G
= 10μ" (0,25 μm)
Gold on contact

ASSEMBLED LENGTH

-“XX.XX”
= Assembled Length in Inches (76,20 mm)
03.00" min. for -S end option
(82,60 mm)
03.25" min. for -D end option

END OPTION

-S
= Single Ended
-D
= Double Ended
-T
= Transfer End Terminal on End 1 Socket on End 2 (See chart for End 2 option)
-TF
= Transfer End with Friction Lock (-05 & -07 positions not available.)
-TR
= Transfer End with Retention Latch (TFM -WT option required for mating)

END 2 OPTION

Requires -D, -TF or -TR (End 1 Notch Down).
-NUS
= Notch up, straight (Pin 1 to Pin 2)
-NDS
= Notch down, straight (Pin 1 to Pin N-1)
-NUX
= Notch up, crossed (Pin 1 to Pin 1)
-NDX
= Notch down, crossed (Pin 1 to Pin N)

END 2	END OPTION
T-NUS	Pin 1 to Pin N
T-NDX	Pin 1 to Pin 1
T-NUX	Pin 1 and Pin N-1
T-NDX	Pin 1 to Pin 2

ALSO AVAILABLE (MOQ Required)

- Color coded cable (*Teflon® N/A)
 - Other plating options
- Contact Samtec.

*DuPont™ Teflon® is a registered trademark of the E.I. du Pont de Nemours and Company or its affiliates.

Note: For wiring option and pin position location information, refer to drawings on web.

Note: Teflon® cable is intended for crimp only. Contact Samtec for solderable cable applications.

Note: Some lengths, styles and options are non-standard, non-returnable.

