

OSR-5-M-Low lens for Dragon LEDs





- Designed for Dragon LEDs.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F)
- High optical efficiency, >85%
- No lens holder. Snap-fitting of the lens to customer's heat sink. Please contact us for detailed mounting information
- Diameter 35.5 mm (MR11)

LENS TYPES

NAME	ORDERING CODE	FWHM Angle
OSR-5 Medium	C10472_OSR-5-M-Low	±12°

MEASUREMENT DATA & PHOTOGRAPHS


OSR-5-M



PACKAGING

Lenses are packed in carton boxes of 500 pieces in each box.

DIMENSIONS & PCB LAYOUT



© Ledil Oy – PRELIMINARY - Subject to change without prior notice