




Tank Adaptors, PVC-U


End connection: union with solvent cement socket, ISO

Gasket: Flat gasket EPDM



d	Code	£	d ₁	L	L ₁	L ₂	L ₃ max.	L ₄	G	s	Diameter of bore in tank side mm	Weight kg
mm			mm	mm	mm	mm	mm	mm	inch	mm		
3/8	161 050 225	10.50	44	85	65	10	32	14	3/4	33	28	0.073
1/2	161 050 226	11.20	56	89	67	11	30	16	1	46	35	0.131
3/4	161 050 227	12.10	65	97	72	12	32	19	1 1/4	50	43	0.194
1	161 050 228	13.40	70	103	75	12	33	22	1 1/2	60	49	0.255
1 1/4	161 050 229	16.10	95	111	78	12	32	26	2	80	61	0.446
1 1/2	161 050 230	18.20	95	119	82	13	32	31	2 1/4	80	67	0.455
2	161 050 231	35.90	115	131	87	13	33	38	2 3/4	95	83	0.674

21 91 39




Nipple (PVC-U plain spigot x PVC-U threaded spigot)

d	(R)	PN	Code	£	SP	GP	g		l			
3/8		9	721.913.905	1.10	10		10		43			
1/2		9	721.913.906	1.25	10		15		50			
3/4		9	721.913.907	1.45	10		20		56			
1		9	721.913.908	2.25	10		30		63			
1 1/4		9	721.913.909	2.85	5		40		75			
1 1/2		9	721.913.910	3.25	5		60		88			
2		9	721.913.911	4.05	5		80		88			
3		9	721.913.913	12.20	2		300		128			
4		9	721.913.915	16.50	2		560		153			

Thread: BSP taper male.

21 96 07




Hose Connector

d	(R)	PN	Code	£	SP	GP	g		d ₁	l	s	
1/4		10	721.960.704	1.12	1		5		12	59	14	
3/8		10	721.960.705	1.20	10		11		16	67	19	
1/2		10	721.960.706	1.80	10		19		20	86	22	
3/4		10	721.960.707	2.40	5		28		25	92	27	
1		10	721.960.708	2.90	5		48		30	103	36	
1 1/4		10	721.960.709	3.98	5		79		40	115	46	

Thread: BSP taper male. Dimension s is across flats.

21 55 14



Tap Connector

d	PN	Code	£	SP	GP	g		D	l ₁	l ₂	s
3/8 x 1/2	15	721.551.405	3.40	5		15		23	39	55	24
1/2 x 3/4	15	721.551.406	4.10	5		18		27	43	60	31

PVC-U plain socket x BSP brass nut and washer. Dimension s is across flats.