


IDC-Connector 2,54 mm

Series

101



Rated current	1,0 A
Rated voltage	250 VRMS / VDC
Please consider air- and creepage distances	
Withstand voltage	500 VRMS for 1 minute
Material contact	Phosphor bronze
Material insulator	Thermoplast UL94V-0
Operating temperature	-40°C to +105°C

pitch
2,54

mating pin
size


□ 0,64

max.
pincount
064


All dimensions in mm.

Variation

Recommended cable: AWG 28 flat ribbon cable with 1,27 mm centerline.



1



2

no. of contacts	see figure left	see figure left	available in variation	
n	A	B		
006	12,32	5,08	1	2
008	14,86	7,62	1	2
010	17,34	10,16	1	2
012	19,94	12,70	1	2
014	22,48	15,24	1	2
016	25,02	17,78	1	2
018	27,56	20,32	1	2
020	30,10	22,86	1	2
024	35,18	27,94	1	2
026	37,72	30,48	1	2
030	42,80	35,56	1	2
034	47,88	40,64	1	2
040	55,50	48,26	1	2
050	68,20	60,96	1	2
060	80,90	73,66	1	2
064	85,98	78,74	1	2

Plating:
S = Selective Au

Variation (1,2)

No. of contacts

Plating contact



www.mpe-connector.de

CS190811_V2

Order code:

101-2-222-S-B S0

Mating series	093	092
see page	3-47	3-48