


ED114/XDS



2-12 poles, Spacing 7.5 mm

insert required no. of poles **x**

How to order see page 5



Ratings:

Rated Voltage	300V	500 V
Rated Current	15 A	32 A (T60)
Wire Size	AWG 22-12	4.0 mm²
Test Voltage		3.0 kV
Rated Torque/ScrewSize		0.8 Nm/M3

Max. Rated Cross Section

Single Wire (solid)	4.0 mm²
Stranded Wire (flexible)	2.5 mm²
Stranded wire with Ferrules	1.5 mm²

Dimensions

Spacing	7.5 mm
PCB Hole Diameter	2.0 mm X 2.8 mm
Stripped Length	7.0 mm

Materials

Insulating Material	PA
Flammability Class	UL94 V-0
Temperature Range	-30°C/+105°C
Terminal Block	CuZn
Wire Guard	Stainless Steel

Color

Grey

