



English | 简体中文 | 日本語

Search by Part Number



Search Site by keyword



Contact IDT | Investors | Press

About IDT

Products

Applications

Support

myIDT

Calculators | Cross Reference | Green Initiative | Military | Parametric Search | Search by Part Number, Keyword, Document, Green/Pb-Free, Package

Home > Products > > 960013 > 960013BFLF

You may also like...

960013BFLF

Category:

Generic Part: 960013

Market Group: PC CLOCK

Description: PC SPECIAL PURPOSE

Output Features:

- 1 CPUCLK @ 3.3V up to 133.3 MHz
- 1 ASICCLK @ 3.3V up to 133.3 MHz
- 6 SDRAMs @ 3.3V up to 133.3MHz
- 6 PCIs @ 3.3V (including 1 free-running)
- 1 REF @ 3.3V, 14.318MHz
- 1 SDCLK @ 3.3V, 42MHz to 50MHz
- 1 MCLK @ 3.3V up to 133.3 MHz

Time is
money

Parameters

Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	Yes
Minimum Order Quantity	120
Factory Order Increment	30

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

Type	Title	Size	Revision Date
Misc	PC Clocks Contact Info	61 KB	05/29/2007

Package

Package	SSOP 48 (PVG48)
Description	SSOP 300 MIL
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	F
Package Type	SSOP
Lead Count	48
Length	15.9 mm
Width	7.5 mm
Thickness	2.3 mm
Pitch	0.64 mm
Tube / Tray	TUBE
Quantity per Tube/Tray	30
Quantity per Reel	1000
Moisture Sensitivity Level (MSL)	1
Moisture Exposure Floor Life	Unlimited@<30C/85% RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	NA
Related Package Documents	view documents

Home | Site Map | Legal | Careers | Contact Us | Quality | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. All Rights Reserved.