

Waber-by-Tripp Lite Power Strip with 10 Side-by-Side Outlets and 15-ft. Cord

MODEL NUMBER: **UL800CB-15**



Description

The Waber-by-Tripp Lite UL800CB-15 Power Strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage. Includes 15 foot AC line cord and flat sheet metal flanges for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15 amp resettable circuit breaker and attractive blue/gray color scheme. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 10 NEMA 5-15R ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle) FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment.
- Includes 10 NEMA 5-15R output receptacles arranged with traditional wall socket spacing to accept large equipment plugs with minimal outlet blockage
- Lighted on/off switch controls power to all outlets
- Keyhole mounting tabs for installation in a wide variety of applications
- UL Recognized Component, Tested to UL1363 (Power Tap), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15 foot AC line cord

Highlights

- 10 outlets
- 15 ft. cord
- 17.5" length
- Lighted master switch
- All metal housing

Applications

- Offers reliable, convenient, cost effective method of power distribution for appliances, power tools, lighting and other electrical equipment. Unfiltered electrical pass-through makes UL800CB-15 ideal for distributing alternate waveform UPS or generator power to protected equipment.

Package Includes

- UL800CB-15 Power Strip
- Warranty information
- Instruction manual

Specifications

OVERVIEW	
Intended Application	Home/Office; Industrial/Factory Floor
Style	Strip



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet Quantity / Type	10 NEMA 5-15R
Number of Outlets	10
Outlet Orientation	Two rows of 5 outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	Nema 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted 2 position switch controls power to all outlets
PHYSICAL	
Unit Dimensions (hwd / in.)	17.5 x 4 x 1.75
Unit Dimensions (hwd / cm)	44.5 x 10.2 x 4.4
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 71.45mm; Distance between vertical outlets = 38.90mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between end tabs = 462.30mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL Recognized Component, Tested to UL1363 (Power Tap)
cUL / CSA (Canada)	cUL
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.