



Dimensions: mm (in.)



Electrical Specifications:

- Contact Rating: 1mA/10VDC
- Contact Resistance: $\leq 10\Omega$
- Isulation Resistance: $\geq 50M\Omega$ 50V DC
- Dielectric Strength: 50V AC 1 minute

Mechanical Specifications:

- Operating Force: $25\pm 10\text{gf}$
- Operating Temperature: $-10^\circ\text{C} \sim +60^\circ\text{C}$
- Number and Postions of Segment Points: 12 Segment points (each segment angle: $30^\circ\pm 3^\circ$)
- Output Resolution: 6 pulse/360°

Note:

- RoHS Compliant

Encoder
101-5429-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-5429-EV](#)