





- 1 TYCO TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING.
- 2 THESE DIMENSIONS PERTAIN TO CAVITY C'S ONLY – NOT TO CONTACT LOCATIONS
- 3 THESE DIMENSIONS ARE DESIGNED FOR .0625±.0075 THICK PC BOARD
- 4 DUPLEX PLATED, .00030 GOLD ON CONTACT AREA, .000150–.000300 BRIGHT TIN–LEAD OR TIN ON SOLDER LEADS, ALL OVER .000050 NICKEL.
- 5 POINT OF MEASUREMENT FOR PLATING THICKNESS (MEASURED INSIDE CONTACT BEAMS)
- 6 NO PART NUMBER MARKING REQUIRED FOR THIS PART
- 7 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE LOCATION SHOWN.
- 8 POINT OF CONTACT MEASUREMENT.
- 9 HOUSING; GLASS FILLED, FLAME RETARDANT POLYESTER
COLOR–BLACK
CONTACTS: PHOSPHOR BRONZE.
- 10 DUPLEX PLATED: .000030 GOLD ON CONTACT AREA, .0001500–.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL.
- 11 ROHS 2002/95/EC COMPLIANT
- 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	6	10	3.200	3.100	31	64	11	7-87331-9	
		10	3.100	3.000	30	62	11	7-87331-8	
		10	2.900	2.800	28	58	11	7-87331-7	
		10	2.800	2.700	27	56	11	7-87331-6	
		10	2.300	2.200	22	46	11	7-87331-5	
		10	1.800	1.700	17	36	11	7-87331-4	
		10	1.600	1.500	15	32	11	7-87331-3	
		10	1.100	1.000	10	22	11	7-87331-2	
		10	.600	.500	05	12	11	7-87331-1	
		10	.900	.800	08	18	11	7-87331-0	
		10	2.700	2.600	26	54	11	6-87331-9	
		10	1.700	1.600	16	34	11	6-87331-8	
		10	1.300	1.200	12	26	11	6-87331-7	
		10	1.200	1.100	11	24	11	6-87331-6	
		10	.700	.600	06	14	11	6-87331-5	
		10	2.100	2.000	20	42	11	6-87331-4	
		10	2.600	2.500	25	52	11	6-87331-3	
		10	2.200	2.100	21	44	11	6-87331-2	
		10	3.000	2.900	29	60	11	6-87331-1	
		10	1.500	1.400	14	30	11	6-87331-0	
6	6	10	.500	.400	04	10	11	5-87331-9	
		10	2.500	2.400	24	50	11	5-87331-8	
		10	2.400	2.300	23	48	11	5-87331-7	
		10	.400	.300	03	8	11	5-87331-6	
		10	.800	.700	07	16	11	5-87331-5	
		10	1.000	.900	09	20	11	5-87331-4	
		10	1.400	1.300	13	28	11	5-87331-3	
		10	1.900	1.800	18	38	11	5-87331-2	
		10	2.000	1.900	19	40	11	5-87331-1	
		12	6	12	OBSOLETE	4	3.200	3.100	31
12	OBSOLETE			4	3.100	3.000	30	62	2-87331-8
12	OBSOLETE			4	2.900	2.800	28	58	2-87331-7
12	OBSOLETE			4	2.800	2.700	27	56	2-87331-6
12	OBSOLETE			4	2.300	2.200	22	46	2-87331-5
12	OBSOLETE			4	1.800	1.700	17	36	2-87331-4
12	OBSOLETE			4	1.600	1.500	15	32	2-87331-3
12	OBSOLETE			4	1.100	1.000	10	22	2-87331-2
12	OBSOLETE			4	.600	.500	05	12	2-87331-1
12	OBSOLETE			4	.900	.800	08	18	2-87331-0
12	OBSOLETE			4	2.700	2.600	26	54	1-87331-9
12	OBSOLETE			4	1.700	1.600	16	34	1-87331-8
12	OBSOLETE			4	1.300	1.200	12	26	1-87331-7
12	OBSOLETE			4	1.200	1.100	11	24	1-87331-6
12	OBSOLETE			4	.700	.600	06	14	1-87331-5
12	OBSOLETE			4	2.100	2.000	20	42	1-87331-4
12	OBSOLETE			4	2.600	2.500	25	52	1-87331-3
12	OBSOLETE			4	2.200	2.100	21	44	1-87331-2
12	OBSOLETE			4	3.000	2.900	29	60	1-87331-1
12	OBSOLETE			4	1.500	1.400	14	30	1-87331-0
12	6	12	OBSOLETE	4	.500	.400	04	10	-87331-9
		12	OBSOLETE	4	2.500	2.400	24	50	-87331-8
		12	OBSOLETE	4	2.400	2.300	23	48	-87331-7
		12	OBSOLETE	4	.400	.300	03	8	-87331-6
		12	OBSOLETE	4	.800	.700	07	16	-87331-5
		12	OBSOLETE	4	1.000	.900	09	20	-87331-4
		12	OBSOLETE	4	1.400	1.300	13	28	-87331-3
		12	OBSOLETE	4	1.900	1.800	18	38	-87331-2
		12	OBSOLETE	4	2.000	1.900	19	40	-87331-1
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					
		12	OBSOLETE	4					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J KNAUB 05-01-94		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK A GABANY 28-06-94		NAME ASSEMBLY, MOD II, DOUBLE ROW, .100x.100 VERTICAL BOARD MOUNT, CARD EDGE —	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A GABANY 28-06-94			
 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC —			
MATERIAL		APPLICATION SPEC —			
		FINISH		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
CUSTOMER DRAWING				DRAWING NO C-87331	
				RESTRICTED TO —	
				SCALE 1:1 SHEET 1 of 1 REV 111	