





ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
811	C	Obsolete parts removed--was #HSS-**	JWM	3/20/01	JC	3/21/01	JC	3/21/01
1865	D	RoHS ADDED	DCM	10/17/05	JWM	10/18/05	JWM	10/18/05



SPC Type No.	Length	"H"	"D" ±.005 [±.13]	Self-tapping Screw Size
HSS-44	1/2 [12.7]	.187 ±.006 [4.8 ±.15]	.102 [2.6]	4
HSS-46	3/4 [19.1]			
HSS-48	1 [25.4]			
HSS-64	1/2 [12.7]	.250 ±.008 [6.4 ±.20]	.110 [2.8]	6
HSS-66	3/4 [19.1]			
HSS-68	1 [25.4]			
HSS-85	5/8 [15.9]	.375 ±.010 [9.5 ±.25]	.141 [3.6]	8
HSS-86	3/4 [19.1]			
HSS-88	1 [25.4]			

NOTES:

1. Material: CPVC
2. Color: Light Gray
3. Self-Extinguishing - Rated: UL94V-0
4. Mounts with Self-Tapping screw



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Tolerances Unless
Otherwise Specified
.XX = ±.010
.XXX = ±.005
Frac. = ± 1/64

DRAWN BY:

JAP

DATE:

3/26/93

CHECKED BY:

JC

DATE:

3/29/93

APPROVED BY:

JL

DATE:

3/29/93

DRAWING TITLE:

Hex Spacer Standoffs

SIZE

A

DWG. NO.

TA-314

ELECTRONIC FILE

TA-314.dwg

REV

D

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1