



REDINGTON

What the world is counting on.

The Redington Model 732 provides a DC Hour Meter with an operating range of 10-80VDC. Models are protected for two times battery voltage and/or reverse polarity. Models are available in the standard industry housings. Its quartz time base insures accurate long-term time keeping. The Totally Sealed case protects against the environment and provides years of reliable service. All applicable models are NEMA 4X, 12 rated when mounted with optional gasket.

Features

- Operating voltage 10-80VDC
- Totally Sealed
- UL/cUL Recognized, CE & RoHS Compliant, NEMA & SAE
- 6 Figure, 99999.9
- Quartz accuracy

Options

- Wire leads
- Gaskets (for NEMA 4X, 12 rating)
- Custom Labeling
- Custom Terminals (up, down, straight)
- Adapter bezels for various panels

Specifications

Figures:	6 - digits, 0.14" [3.6mm] 99999.9 Hours and running indicator - white on black Decimal - black on white
Reset:	Non-reset
Voltage:	10-80VDC
Power:	1 watt max.
Mounting:	Clip, Mounting Holes, Cup, or Stirrup
Termination:	¼" [6.3mm] spade terminals
Weight:	~2.0 oz [57 g]
Accuracy:	± 0.02% over entire range
Bezel:	Stirrup and Cup mount have polished stainless steel bezels
Case Material:	Black polymer
Lens Material:	Cup & Stirrup - Glass; Other Models - Polymer
Transient Protection:	± 6 times normal for 300msec
Agency Approvals:	UL/cUL Recognized, CE & RoHS Compliant, SAE & NEMA 4X, 12 Compliant
Overvoltage & Reverse Polarity:	Protected for 2 times battery voltage and/or reverse polarity
Environmental:	Totally Sealed
Front Panel:	NEMA 4X, 12 rated with optional gasket
Temperature:	-40°F to +185°F [-40°C to + 85°C]
Humidity:	95% (SAE J1378)
Shock:	55g @ 9 - 13msec (SAE J1378)
Vibration:	10-80Hz. 20g max. (SAE J1378)

Models

732-0001	3-Hole, Round
732-0002	Flush, Rectangular, Clip
732-0003	Flush, Round, Clip
732-0004	2-Hole, Rectangular
732-0013*	Panel mt, Round, Cup
732-0023*	Panel mt, Round, Stirrup
732-0030*	48mm Sq. Panel, Clip

Description

Optional Accessories

5003-011 (NEMA 4X, 12 Gasket)
5003-009 (NEMA 4X, 12 Gasket)
5003-008 (NEMA 4X, 12 Gasket)
5003-010 (NEMA 4X, 12 Gasket)
1662-026 (55mm Sq. Panel Adapter)
1662-024 (72mm Sq. Panel Adapter)
1662-025 (72mm Rd. Panel Adapter)

*Gasket Not Available

Applications

Agricultural Equipment



Utility Vehicles



Construction Equipment



Pressure Washers



Outdoor Power Equipment



MODEL 732

DC HOUR METERS

- ✓ Reliability
- ✓ Precision
- ✓ Quality
- ✓ Value





REDINGTON

What the world is counting on.

The Redington Model 722 provides an AC Hour Meter with an operating range of 90-264VAC 50/60 Hz. You no longer require two separate meters, one for 115VAC and one for 230VAC. Models are available in the standard industry housings. Its quartz time base insures accurate long-term time keeping. The Totally Sealed case protects against the environment and provides years of reliable service. All applicable models are NEMA 4X, 12 rated when mounted with optional gasket.

Features

- Operating voltage 90-264VAC 50/60Hz
- Totally Sealed
- UL/cUL Recognized, CE & RoHS Compliant, SAE & NEMA
- 6 Figure, 99999.9
- Quartz accuracy

Options

- Wire leads
- Gasket kit (for NEMA 4X, 12 rating)
- Custom Labeling
- Terminals up, down, straight
- Adapter bezels for various panels

Specifications

Figures:	6 - digits, 0.14" [3.6mm] 99999.9 Hours and running indicator - white on black Decimal - black on white
Reset:	Non-reset
Voltage:	90-264VAC
Frequency:	50/60Hz
Power:	1 watt max.
Mounting:	Clip or Mounting Holes
Termination:	1/4" [6.3mm] spade terminals
Weight:	~2 oz [57 g]
Accuracy:	± 0.02% over entire range
Case Material:	Black polymer
Lens Material:	Polymer
Agency Approvals:	UL/cUL Recognized, CE & RoHS Compliant, SAE & NEMA 4X, 12 Compliant
Environmental:	Totally Sealed
Front Panel:	NEMA 4X, 12 rated with optional gasket
Temperature:	-40°F to +185°F [-40°C to + 85°C]
Humidity:	95% (SAE J1378)
Shock:	55g @ 9 - 13msec (SAE J1378)
Vibration:	10-80 Hz. 20g max. (SAE J1378)

Models	Description	Optional Accessories
722-0001	2-Hole, Rectangular	5003-010 (NEMA 4X, 12 Gasket)
722-0002	Flush, Rectangular, Clip	5003-009 (NEMA 4X, 12 Gasket)
722-0003	Flush, Round, Clip	5003-008 (NEMA 4X, 12 Gasket)
722-0004	3-Hole, Round	5003-011 (NEMA 4X, 12 Gasket)
722-0030*	48mm Sq. Panel, Clip	1662-026 (55mm Sq. Panel Adapter) 1662-024 (72mm Sq. Panel Adapter) 1662-025 (72mm Rd. Panel Adapter)

*Gasket Not Available

Applications

Floor scrubbers



Air Compressors



Control Panels



Generators



Oxygen Concentrators



Irrigation Systems




Tanning Booths



Phone: (860) 688-6205

www.redingtoncounters.com

Fax: (860) 688-1591



MODEL 722

AC HOUR METERS

- ✓ Reliability
- ✓ Precision
- ✓ Quality
- ✓ Value