

Technical Specifications

Tungsten halogen & Dichroic lamps

Ring Commercial have made a conscious commitment to supplying only good quality Tungsten Halogen and Low Voltage Dichroic lamps.
The major benefits of our products are :-

- > All Dichroics feature Toshiba reflector which is superior in quality to Chinese, Korean and Japanese coated reflectors.
- > All Dichroics are fitted with nickel plated pins to make the lamps extremely robust.
- > Tungsten Halogen Lamps feature welded filament support rings to reduce instances of breakage.
- > All lamps are rigorously tested to British Standards guidelines.

Linear Tungsten halogen Lamp - Double Ended

Code	Wattage	Voltage	Lumens	Col. Tem	Length	Avg.Life	Base	Filament
TH15024	150w	240v	2400	3000k	78mm	2000hrs	R7s	C-8
TH20011	200w	110v	3200	3000k	118mm	2000hrs	R7s	C-8
TH30011	300w	110v	5900	3000k	118mm	2000hrs	R7s	C-8
TH50011	500w	110v	10000	3000k	118mm	2000hrs	R7s	C-8
TH75011	750w	110v	16000	3000k	189mm	2000hrs	R7s	C-8
TH1K11	1000w	110v	22000	3000k	189mm	2000hrs	R7s	C-8
TH20024	200w	240v	2800	3000k	118mm	2000hrs	R7s	C-8
TH30024	300w	240v	5000	3000k	118mm	2000hrs	R7s	C-8
TH50024	500w	240v	9500	3000k	118mm	2000hrs	R7s	C-8
TH75024	750w	240v	15000	3000k	189mm	2000hrs	R7s	C-8
TH1K24	1000w	240v	21000	3000k	189mm	2000hrs	R7s	C-8
TH15K24	1500w	240v	33000	3000k	254mm	2000hrs	R7s	C-8

MR 16 Dichroic Reflector lamp (51mm)

Code	Voltage	Wattage	Beam Angle	Luminous Output cd	Colour Temp	Avg.Life	Style	Ansi Code
DLM49	12v	50w	13 degree	9150	3000k	2000hrs	Open	EXT
DLM49E		50w	13 degree	9150	3000k	2000hrs	Sealed	EXT
DLM50		50w	24 degree	3000	3000k	2000hrs	Open	EXZ
DLM50E		50w	24 degree	3000	3000k	2000hrs	Sealed	EXZ
DLM58		50w	38 degree	1500	3000k	2000hrs	Open	EXN
DLM58E		50w	38 degree	1500	3000k	2000hrs	Sealed	EXN
DLM61		75w	38 degree	2000	3000k	2000hrs	Open	EYC
DLM61E		75w	38 degree	2000	3000k	2000hrs	Sealed	EYC
DLM68		20w	12 degree	3300	3000k	2000hrs	Open	ESX
DLM68E		20w	12 degree	3300	3000k	2000hrs	Sealed	ESX
DLM69		20w	36 degree	460	3000k	2000hrs	Open	BAB
DLM69E		20w	36 degree	460	3000k	2000hrs	Sealed	BAB