

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0741821002](#)
Status: **Obsolete**
Description: 1.27mm (.050") Pitch SCSI+ Receptacle, Unshielded, Right Angle, Low Cost Version, 68 Circuits
Replacement Part Number: [71061](#)

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	74182
Application	Board-to-Board
Comments	Reverse Retentive PC Tail
Component Type	Receptacle
Product Name	SCSI+
Replacement Part Number	71061
Type	N/A

Physical

Circuits (Loaded)	68
Circuits (maximum)	68
Durability (mating cycles max)	500
Flammability	94V-0
Lock to Mating Part	None
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Right Angle
PC Tail Length	3.18mm (.125")
PCB Retention	N/A
PCB Thickness - Recommended	1.60mm (.063"), 2.40mm (.094")
Packaging Type	Tube
Panel Mount	No
Pitch - Mating Interface	1.27mm (.050")
Plating min - Mating	0.381µm (15µ")
Plating min - Termination	1.905µm (75µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +75°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	No
Voltage - Maximum	30V

Material Info

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74182Series](#)

Mates With
[70498](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION