

Signal lamps with integrated filament lamp - 14 mm, round lens, 24 - 28 V, green lens
1.69.523.003/1502


Approvals

VDE	VDE T85° (only version with neon lamp)
-----	--

General information

Form of lens	round
Colour of lens	transparent green

Dimensions

Dimensions of collar	ø18 x 4 mm
Overall height	4 mm
Mounting depth	31.5 mm
Mounting hole	14 mm

Mechanical design

Mounting	pressing into hole
Terminals	quick connector 2.8 x 0.8 mm
Lamp socket	no
Lamp	filament lamp

Electrical characteristics

Voltage limit max.	28 V
Power limit max.	1.2 W

Other specifications

Operating life	10,000 h
Degree of protection from front side	IP40
Weight	5 g
Approvals 1,5 mA (T °C)	VDE, SEV, FEMKO, DEMKO

Panel cut-out


