

NOTES: UNLESS OTHERWISE SPECIFIED


1. P/N: 9205-HS
INSULATOR: HEAT SHRINK TUBING 221. BLACK.
BODY: BRASS. 40μ [1.02μm] MIN GOLD OVER NICKEL
PLATED.

CONTACT: BeCu OR PHOSPHOR BRONZE. 40μ [1.02μm]
MIN GOLD OVER NICKEL PLATED.

2. P/N: 9210COLOR
HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
END CAP: MACHINED DELRIN. WHITE.
FRAME: BRASS. NICKEL PLATED.

3. P/N: W-200/COLOR
22AWG 65X40 TINNED COPPER
0.070 [1.78] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 2.5 AMPS
MAXIMUM VOLTAGE: 1000 (300 UL) W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
±	.XX ±	±	±		
MATERIAL SEE NOTE.		DRAWN	R.L.		
FINISH SEE NOTE.		APPROVED BY			
NEXT ASSY		USED ON		SIZE CODE IDENT NO. DRAWING NO.	
APPLICATION		DO NOT SCALE DRAWING		DESCRIPTION 0.025 [0.64] SQ. SOCKET TO STD BAN SKT (9210)	
				SCALE 1:1	
				SHEET 1 OF 1	