



LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	18 DAP
				B		REV & REDRAWN PER 0720-0040-93	3-17-93		

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE		UL E13288 Listed	
16-14HD AWG	SOLID OR STRANDED	16-14HD AWG	STRANDED
16-14HD AWG	SOLID OR STRANDED	MILITARY P/N AND CLASS	
16-14HD AWG	SOLID OR STRANDED	NOT APPLICABLE	



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:	170°C MAX
VOLTAGE RATING:	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:	1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ± ANGLES	FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727
--	--

DR 3-17-93 TA BRINKMAN	CHK 3-17-93 DA PATTERSON
APPD 3-17-93 DE MILLER	APPD 3-17-93 JL MECKLEY
PRODUCT SPEC	

NAME AMP AMP Incorporated Harrisburg, PA 17105-3608	SIZE CAGE CODE 00779 DRAWING NO G=320758
---	--

TERMINAL, RING TONGUE,
HEAVY DUTY, SOLISTRAND™

SCALE 4:1	SHEET 1 OF 1
--------------	-----------------