




FS75-8-DSL3



- Polypropylene insulation housing available in DIN standard colors in strips of 50
- Continuously molded design provides consistent placement of ferrules in tool to ensure fast, reliable terminations
- Available in #20 – #14 AWG featuring a seamless barrel design to contain loose wire strands for superior terminations
- Designed for use with the Semiautomatic Ferrule Crimping Tool CT-1000 for medium volume applications

■ Part Number	FS75-8-DSL3
■ RoHS Compliancy Status	Compliant
■ Part Description	Insulated ferrules, single wire French end sleeve on strip.
■ Color	Orange
■ Length (In.)	.60
■ Length (mm)	15.2
■ CE Compliant	No
■ CE Marking	No
■ Inside Diameter (In.)	.04
■ Inside Diameter (mm)	1.0
■ Max. Wire Insul. Dia. (In.)	.10
■ Pin Length (In.)	.31
■ Pin Length (mm)	8.0
■ Pricing Description	Insulated Ferrules on Strips, single wire, 20 AWG (.50mm), .31"(8.0mm) pin length, orange end sleeve
■ Tool	CT-1000
■ Wire Range	20 AWG
■ Wire Range (mm²)	0.50
■ Wire Strip Length (In.)	13/32
■ Wire Strip Length (mm)	10