


RNF100




Dimensions (in millimetres)

| Part Number   | Inside Diameter                    |                                       | Wall Thickness                        |
|---------------|------------------------------------|---------------------------------------|---------------------------------------|
|               | D (min)<br>Expanded<br>as supplied | d (max)<br>Recovered<br>after heating | W (nom)<br>Recovered<br>after heating |
| RNF100 NR.541 | 6.0                                | 1.6                                   | 0.5                                   |
| RNF100 NR.610 | 5.3                                | 1.6                                   | 0.5                                   |

RNF 100 NR. 541 Available in colours only (not clear)

RNF 100 NR. 610 Available in colours and clear.

Issued by



Issue 2

Date 7 March 1978

Approved by

