

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > Search=BIT-4* > BIT-4

BIT-4



BIT-4

14-4 ONE SIDED UNITAP

ACTIVE

Customer Drawing

RoHS compatible

Electrical division

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Download document

Literature

> Oxide Inhibitor Unitap Material Safety Data Sheet

> Power solutions Product Focus

> Insulated Multiple Connectors Brochures

> Aluminum Products Brochure

> UNITAP Insulated Multiple Tap Connectors

Application Tooling

> Electrical Tooling

Brochure

> Renewable Energy Products Brochure

> EC&M Catalog

> Connector Theory and Application Brochure

Specifications

General	Dimensional	Physical	Approvals / Certifications	Other Features
<u>General</u>				
Number of Ports			2	
<u>Dimensional</u>				
Height (in)			1.26 in.	
Length (in)			1.16 in.	
Width (in)			1.26 in.	
Wire Entry			Double	
Hex Size (Key)			Slotted	
<u>Physical</u>				
Conductor Size			4 AWG	
			8 AWG	
			12 AWG	
			10 AWG	
			14 AWG	
			6 AWG	
Conductor Size (Range)			14 AWG to 4 AWG	
<u>Approvals / Certifications</u>				
UL Listed			Yes	
CSA Certified			No	
<u>Other Features</u>				
UPC			78181013414	
Keyword			unitap	