




FEATURES:

- Dual Purpose
- Insulates all hot leads when used as an extension cord.
- Endless extension couplings possible with any banana plug patch cord.

MATERIALS:

Conn: Banana Plug

Material: Spring, One piece heat treated Beryllium Copper, Berylco 25 per QQ-C-533.

Finish: Nickel plate per QQ-N-290 class 2 (.0002 min.).

Insulation: Polypropylene, molded to plug body and wire. Color matches color of wire.

Operating Temperature: +55° C. (+131° F.) Max.

Marking: "POMONA ELECTRONICS CALIF."

Wire: 18 AWG; stranding 65 x 36 tinned copper, polyvinyl chloride insulated (.050 wall thickness).

Marking: POMONA 4702-"XX".

Conn: In-Line Banana Jack

Material: Brass, H.H. per QQ-B-626, Alloy 360.

Finish: Nickel plate per QQ-N-290. Class 2 (.0002 min.).

Insulation: Polypropylene, molded to jack body and wire. Color matches color of wire.

Operating Temperature: +55° C. (+131° F.) Max.

Marking: "POMONA ELECTRONICS CALIF."

RATINGS: Entire Assembly

Operating Temperature: +55° C. (+131° F.) Max.

Operating Voltage: 5000 W VDC

Current: 15 Amperes Cont.

ORDERING INFORMATION: Model 4702-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 18" (475), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths can be quoted upon request.

*=Color, -0 black, -2 red.

Ordering Example: 4702-60-2 Indicates 60" in length, color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4702-18-2](#) [4702-12-0](#) [4702-12-2](#) [4702-18-0](#) [4702-60-2](#)