





REV.	DATE	DESCRIPTION
NC	10/31/07	INITIAL RELEASE



RECOMMENDED
MOUNTING HOLE

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	10/31/07						
7						CHECKED								
6						ISSUED				PART DESCRIPTION BNC PCB PUSH ON RECEPTACLE				
5						SHEET	1 OF 1							
4														
3	CONTACT PIN	BRASS	GOLD	1	PART NO. 112984–10									
2	INSULATOR	TEFLON	NATURAL	1										
1	BODY	BRASS	NICKEL	1	DWG. NO. 112984–10.DWG REV. NC SIZE A SCALE NA									
	DESCRIPTION	MATERIAL	FINISH	QTY										DO NOT SCALE DRAWING