

4

3

2

1


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS |     |                      |         |     |      |
|-----|------|-----------|-----|----------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION          | DATE    | DWN | APVD |
| G   | 14   |           | D   | REV PER OG3A-0656-04 | 20AUG04 | JR  | TM   |

|                                  |                                                                                                           |                                                                                                         |
|----------------------------------|-----------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|
| <b>AMP</b><br>WIRE RANGE         |  Listed<br>FILE E13288 |  LR7189<br>Certified |
| 16-14HD AWG<br>SOLID OR STRANDED | 16-14HD AWG<br>SOLID OR STRANDED                                                                          | 16-14HD AWG<br>SOLID OR STRANDED                                                                        |



- 1 STAMP AMP 16-14HD\* APPROX AS SHOWN  
2 WIRE INSULATION DIA: .105-.200  
3 TONGUE MATERIAL THK: 1.22 ± 0.05 [0.048 ± 0.002]  
4 MATERIAL: BODY - CU PER ASTM B152  
SLEEVE - PVC,  
COLOR - YELLOW W/BLK STRIPE

|     |              |          |
|-----|--------------|----------|
| -   | LOOSE PIECE  | 34825    |
| QTY | PACKAGE TYPE | PART NO. |

## AMP INCORPORATED CUSTOMER SERVICE SYSTEMS


FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER  
1-800-522-6752FOR APPLICATION  
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER  
1-800-722-1111

FOR ORDER ENTRY


1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR  
AMP INCORPORATED. IT IS SUBJECT TO CHANGE  
AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.MAX RECOMMENDED OPERATING  
TEMPERATURE:  
105°C [221°F]VOLTAGE RATING:  
N/ACIRCULAR MIL AREA:  
1.04-2.62mm² [2,050-5,180]  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
MM[INCHES]

MATERIAL

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± -  
1 PLC ± -  
2 PLC ± 0.20 [0.008]  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -

FINISH

TIN PER ASTM B545

DWN 09/29/92

DK SCHRUM

CHK 11/10/92

RE HERSEY

APVD 20AUG04

M BARNABA

PRODUCT SPEC

108-1034

APPLICATION SPEC

NOT AVAILABLE

WEIGHT -

CUSTOMER DRAWING

**tyco**  
**Electronics**Tyco Electronics Corporation  
Harrisburg, Pa 17105-3608NAME  
TERMINAL, RING TONGUE, PLASTI-GRIPSIZE CAGE CODE DRAWING NO RESTRICTED TO  
A3 00779 C-34825 -

SCALE 4:1 SHEET 1 OF 1 REV D