


## CONCEPT™ PANELS

These panels are taller and wider than corresponding NEMA-size panels. Panels are 14 or 12 gauge steel and painted white or have a conductive finish.

*Panels have a formed flange along any side that is longer than 22.20 in. (564 mm). CP2420 and CP2424 have a flange on all four sides.*



**BULLETIN: CWP, CWY, DWDH2**

| Catalog Number | Panel Type    | Panel Size D x E (in.) | Panel Size D x E (mm) | Gauge |
|----------------|---------------|------------------------|-----------------------|-------|
| CP1212         | Painted steel | 10.20 x 10.20          | 259 x 259             | 14    |
| CP1212G        | Conductive    | 10.20 x 10.20          | 259 x 259             | 14    |
| CP1612         | Painted steel | 14.20 x 10.20          | 361 x 259             | 14    |
| CP1612G        | Conductive    | 14.20 x 10.20          | 361 x 259             | 14    |
| CP1616         | Painted steel | 14.20 x 14.20          | 361 x 361             | 12    |
| CP1616G        | Conductive    | 14.20 x 14.20          | 361 x 361             | 12    |
| CP2016         | Painted steel | 18.20 x 14.20          | 462 x 361             | 12    |
| CP2016G        | Conductive    | 18.20 x 14.20          | 462 x 361             | 12    |
| CP2014         | Painted steel | 18.20 x 12.20          | 462 x 310             | 14    |
| CP2014G        | Conductive    | 18.20 x 14.20          | 462 x 310             | 14    |
| CP2416         | Painted steel | 22.20 x 14.20          | 564 x 361             | 12    |
| CP2416G        | Conductive    | 22.20 x 14.20          | 564 x 361             | 12    |
| CP2020         | Painted steel | 18.20 x 18.20          | 462 x 462             | 12    |
| CP2020G        | Conductive    | 18.20 x 18.20          | 462 x 462             | 12    |
| CP2420         | Painted steel | 22.20 x 18.20          | 564 x 462             | 12    |
| CP2420G        | Conductive    | 22.20 x 18.20          | 564 x 462             | 12    |
| CP3020         | Painted steel | 28.20 x 18.20          | 716 x 462             | 12    |
| CP3020G        | Conductive    | 28.20 x 18.20          | 716 x 462             | 12    |
| CP3220         | Painted steel | 30.20 x 18.20          | 762 x 462             | 12    |
| CP4420         | Painted steel | 42.20 x 18.20          | 1072 x 462            | 12    |
| CP5620         | Painted steel | 53.20 x 18.20          | 1351 x 462            | 12    |
| CP2424         | Painted steel | 22.20 x 22.20          | 564 x 564             | 12    |
| CP2424G        | Conductive    | 22.20 x 22.20          | 564 x 564             | 12    |
| CP3024         | Painted steel | 28.20 x 22.20          | 716 x 564             | 12    |
| CP3024G        | Conductive    | 28.20 x 22.20          | 716 x 564             | 12    |
| CP3624         | Painted steel | 34.20 x 22.20          | 869 x 564             | 12    |
| CP3624G        | Conductive    | 34.20 x 22.20          | 869 x 564             | 12    |
| CP4824         | Painted steel | 46.20 x 22.20          | 1173 x 564            | 12    |
| CP4824G        | Conductive    | 46.20 x 22.20          | 1173 x 564            | 12    |
| CP3030         | Painted steel | 28.20 x 28.20          | 716 x 716             | 12    |
| CP3030G        | Conductive    | 28.20 x 28.20          | 716 x 716             | 12    |
| CP3630         | Painted steel | 34.20 x 28.20          | 869 x 716             | 12    |
| CP3630G        | Conductive    | 34.20 x 28.20          | 869 x 716             | 12    |
| CP4230         | Painted steel | 40.20 x 28.20          | 1021 x 716            | 12    |
| CP4230G        | Conductive    | 40.20 x 28.20          | 1021 x 716            | 12    |
| CP3636         | Painted steel | 34.20 x 34.20          | 869 x 869             | 12    |
| CP3636G        | Conductive    | 34.20 x 34.20          | 869 x 869             | 12    |
| CP4236         | Painted steel | 40.20 x 34.20          | 1021 x 869            | 12    |
| CP4236G        | Conductive    | 40.20 x 34.20          | 1021 x 869            | 12    |
| CP4836         | Painted steel | 46.20 x 34.20          | 1173 x 869            | 12    |
| CP4836G        | Conductive    | 46.20 x 34.20          | 1173 x 869            | 12    |
| CP6036         | Painted steel | 58.20 x 34.20          | 1478 x 869            | 12    |
| CP6036G        | Conductive    | 58.20 x 34.20          | 1478 x 869            | 12    |
| CP2442         | Painted steel | 22.20 x 40.20          | 564 x 1021            | 12    |
| CP2442G        | Conductive    | 22.20 x 40.20          | 564 x 1021            | 12    |
| CP3048         | Painted steel | 28.20 x 46.20          | 716 x 1173            | 12    |
| CP3048G        | Conductive    | 28.20 x 46.20          | 716 x 1173            | 12    |
| CP3060         | Painted steel | 28.20 x 58.20          | 716 x 1478            | 12    |
| CP3060G        | Conductive    | 28.20 x 58.20          | 716 x 1478            | 12    |
| CP7236         | Painted steel | 70.20 x 34.20          | 1783 x 869            | 12    |

Catalog number CP4230 is used on CONCEPT disconnect enclosures.