

IZV012-010F-5065C-SA

is a 10W RoHS compliant single 12V output Constant Voltage power supply, of waterproof design, suitable for LED lighting applications both indoors and out.

- Universal Input Voltage
- IP65 design for indoor or outdoor installation
- Low Power 10W unit
- Convection Cooled
- Short circuit & over temperature protections
- Prewired for convenience

## Applications

- LED street lighting
- LED signs
- LED strips and tapes
- LED chain letters
- Outdoor LED lighting
- Display cases
- LED downlights and Office lighting



## 10W 12V IP65 Rated Constant Voltage LED Lighting Power Supply

### H Specification

Part Number	IZV012-010F-5065C-SA
Voltage	12V
Current	830mA
Power	10W
IP Rating	IP65
Input Voltage	100-240V
Input Frequency	50Hz to 60Hz
Input Current	0.085A@230Vac
Leakage Current	<1mA
Power Factor	0.5
Voltage Tolerance	±1V

Efficiency	higher than 68%
Set Up Time	< 1s
Over Load Protection	20% exceed is allowing
Operating Temperature	-10°C to +40°C
Storage Temperature	-20°C to +80°C
Safety Standards	Designed to meet EN61347-1:2001 /EN61347-2-13:2001
EMI Standards	Meets Emissions to EN 55105, EN61547
Dimensions	L65 x W35 x H23mm
Weight	105g

Input Connections	2 core double insulated cable VDE H03VV-F 3G*0.75mm <sup>2</sup> Brown & blue (L=200mm)
Output Connections	2 core double insulated cable for each channel VDE H03VV-F 2G*0.75mm <sup>2</sup> Black & red (L=200mm)



IP65




**ILS**  
INTELLIGENT  
LED SOLUTIONS



Intelligent LED Solutions, 3 Clewater Please, Lower Way, Thatcham, Berkshire, RG19 3RF UK  
Telephone: +44 (0)1635294606 Fax: +44 (0)1635869200 Email: info@led.co.uk www.led.co.uk  
A division of Intelligent Display Solutions

# 10W 12V IP65 Rated Constant Voltage LED Lighting Power Supply

## ★ Mechanical Drawing



Part Number	IZV012-010F-5065C-SA
Voltage	12V
Current	830mA
Power	10W
IP Rating	IP65

Dimensions	L65 x W35 x H23mm
Weight	105g
Input Connections	2 core double insulated cable VDE H03VV-F 3G*0.75mm <sup>2</sup> Brown & blue (L=200mm)
Output Connections	2 core double insulated cable for each channel VDE H03VV-F 2G*0.75mm <sup>2</sup> Black & red (L=200mm)