



Fixing Clips Plated Steel and PVC Liner

• AFCS-Serie



AFCS Fixing Clip, Stainless Steel and PVC Liner.

Material Data


Material	Galvanised Steel (GS), Polyvinylchloride (PVC)
Colour	Metal (ML), Black (BK)
Operating Temperature	-20 °C to +105 °C



Technical Table

Article-No.	Type	Fixing Hole Ø (FH)	Width (W)	Width (W2)	Bundle Ø max.	Colour
166-50600	AFCS10	5.0	16.0	12.7	11.0	Metal (ML), Black (BK)
166-50601	AFCS12	5.0	16.0	12.7	14.0	Metal (ML), Black (BK)
166-50602	AFCS16	5.0	16.0	12.7	17.0	Metal (ML), Black (BK)
166-50603	AFCS20	5.0	16.0	12.7	21.0	Metal (ML), Black (BK)
166-50604	AFCS25	5.0	16.0	12.7	25.0	Metal (ML), Black (BK)
166-50605	AFCS32	5.0	16.0	12.7	34.0	Metal (ML), Black (BK)
166-50606	AFCS40	14.2 x 17.5	29.0	25.4	44.0	Metal (ML), Black (BK)
166-50607	AFCS50	14.2 x 17.5	29.0	25.4	54.0	Metal (ML), Black (BK)
166-50608	AFCS63	14.2 x 17.5	29.0	25.4	70.0	Metal (ML), Black (BK)
166-50609	AFCS75	14.2 x 17.5	29.0	25.4	76.2	Metal (ML), Black (BK)

All dimensions in mm. Subject to technical changes.



Fixing Clips Stainless Steel

• AFCSS-Serie



AFCSS Fixing Clip, Stainless Steel.

Material Data

Material	Stainless Steel (SS316)
Colour	Metal (ML)
Operating Temperature	-100 °C to +400 °C



Technical Table

Article-No.	Type	Fixing Hole Ø (FH)	Width (W)	Bundle Ø max.	Colour
166-50610	AFCSS10	5.0	11.0	11.0	Metal (ML)
166-50611	AFCSS12	5.0	11.0	14.0	Metal (ML)
166-50612	AFCSS16	5.0	11.0	17.0	Metal (ML)
166-50613	AFCSS20	5.0	11.0	21.0	Metal (ML)
166-50614	AFCSS25	5.0	11.0	25.0	Metal (ML)
166-50615	AFCSS32	5.0	11.0	34.0	Metal (ML)
166-50616	AFCSS40	6.9 x 8.8	12.7	44.0	Metal (ML)
166-50617	AFCSS50	6.9 x 8.8	12.7	54.0	Metal (ML)

All dimensions in mm. Subject to technical changes.

