



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
sockets
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm safety system
sets
miscellaneous

company
 portrait
 corporate association
 location maps
 fairs and exhibitions
 jobs
 imprint
 terms and conditions

Home ▶ sockets ▶ 4 mm safety system ▶ sockets ▶ 4 mm safety system ▶ BUELA 300 K

BUELA 300 K

datasheet for BUELA 300 K
article number: 931667100



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 931 667-100	
description:		Multiple-spring wire plug, shatter-proof, flexible insulated sleeve with transverse hole. Lateral supports provide protection against contact when plugged in at right angles. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm².	
typ:		BUELA 300 K schwarz/black	
system:		4mm system	
order number:		931 667-100	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
pin dimensions		4 mm	
type of contact:		pin (spring loaded)	
type of termination:		solder	
rated voltage:		30 VAC / 60 VDC	
rated current:		30 A	
Please consider derating curve!			
contact resistance:		10 mOhm	
material			
contact material:		brass	
contact surface material:		nickel	
housing material:		PVC - P	
environmental conditions:			
temperature range:		-25 °C to +70 °C	
drawing			
			