

PRODUCT FAMILIES	
	Pin Headers and Sockets
	Clips and Insulators
	Banana Plugs and Jacks
	Grabbers, Probes and Spade Terminals
	Test Leads and Patch Cords
	Plunger Test Leads
	Banana Plug Test Leads
	Alligator Clip Patch Cords
	Coaxial Cable Assemblies
	DMM Kits

ISO 9001:2000

Plunger Test Leads

A pioneer and leader in the manufacture of alligator clips, test leads, and banana plugs.

While the founder of **Mueller Electric Company** invented alligator clips, the company has since expanded its product lines into electric test clips, test leads, test accessories, and board to board connectors, sold to qualifying manufacturers and through leading authorized distributors. View our test lead selection and check for available inventory today!

Micro-Plunger Clip on Both Ends



- Model # BU-1010-A-**-*
- Material: Hook-up Wire: #20 (41/36) AWG tinned copper with 105.C PVC insulation; Plunger: nylon housing, stainless steel spring, beryllium copper contact
 - **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
 - *Std. Colors: -0 Black, -2 Red
 - Rating: Hands free testing at 300V Category II, 5 Amps

Mini-Plunger Clip on Both Ends



- Model # BU-1111-A-**-*
- Material: Hook-up Wire: #20 (41/36) AWG tinned copper with 105.C PVC insulation; Plunger: nylon housing, stainless steel spring, beryllium copper contact
 - **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
 - *Std. Colors: -0 Black, -2 Red
 - Rating: Hands free testing at 300V Category II, 5 Amps

Mini-Plunger to Stackable Banana Plug



- Model # BU-1120-A-**-*
- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Hook-up Wire: #20 (41/36) AWG tinned copper with 105.C PVC insulation; Plunger: nylon housing, stainless steel spring and beryllium copper contact
 - **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
 - *Std. Colors: -0 Black, -2 Red
 - Rating: Hands free testing at 300V, 5 Amps

Mini-Plunger to BNC Male with RG58



- Model # BU-1150-C-**-0
- Material: BNC Connector: MIL-C-30912, gold-plated center contact and silver-plated body; Coaxial Cable: shielded RG58C/U, MIL-C-17F, 50 ohm; Plunger: nylon housing, stainless steel spring and beryllium copper contact
 - **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
 - Rating: Hands free testing at 300 VRMS

Mini-Micro-Plunger to Stackable Banana Plug



- Model # BU-1420-A-**-*
- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Hook-up Wire: #20 (41/36) AWG tinned copper with 105.C PVC insulation; Plunger: nylon housing, stainless steel spring and gold-plated, beryllium copper contact
 - **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
 - *Std. Colors: -0 Black, -2 Red
 - Rating: Hands free testing at 300V, 5 Amps

TOOL

SEARCH TOOLS

MUELLER OR DISTRIBUTOR STOCK SEARCH

PART #

SEARCH

TOOL

CROSS COMPETITOR PART #

Choose a Brand

PART #

SEARCH

TOOL

MeterMate® DMM ACCESSORY SELECTOR

Select Meter Make

Select a Make First

TOOL

BUILD A PCB HEADER OR SOCKET

OVER 10,000 IN STOCK!

GO