

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19418-0030](#)
Status: **Active**
Overview: [MX150L™ Sealed Connector System](#)
Description: [MX150L™ 16 Circuit Receptacle for 14-16 AWG Wire, with CPA](#)

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-19417-001 \(PDF\)](#)
[Application Specification AS-19417-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Literature \(PDF\)](#)

Agency Certification

UL E152602

General

Product Family Crimp Housings
Series [19418](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview [MX150L™ Sealed Connector System](#)
Product Literature Order No 987650-2181
Product Name MX150L™

Physical

Circuits (maximum) 16
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Lock to Mating Part Yes
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 5.84mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +125°C

Electrical

Current - Maximum per Contact 18A

Solder Process Data


Max. Cycles at Max. Process Temperature 0

Material Info

UPC 822348526468

Reference - Drawing Numbers

Application Specification AS-19417-001
Product Specification PS-19417-001
Sales Drawing SD-19418-007



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[19418Series](#)

Mates With

19419 , 19429

Use With

[19420](#) Female Crimp Terminal