
Item no.: 282-128
Product description: 2-conductor fuse terminal block for glass cartridge type fuses
without indicator 1/4 x 1 1/4



Produkt kann von Bild abweichen / product may differ

Packing unit 40 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 6 mm ²
Cross section [AWG]	24 - 10 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	10 A
Weight	23.191 g
Color	grey
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	2
Height	56.5 mm
Height	2.224 in
Width	13 mm
Width	0.512 in
Depth	62 mm
Depth	2.44 in

Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
282-128	CCA	NL5470	500	10	6
282-128	CSA	154112-1505033	250	10	24-10
282-128	KEMA	98.2759.05	500		6
282-128	KR	HMB05880-EL001	500/800	10/46	6
282-128	PRS	TE/1718/880590/08	500	10	6
282-128	UR	E45172	600	10	24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected