


ST04-27

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~150	℃
Junction Temperature	T _j		150	℃
Peak Surge Reverse Current	I _{RSM}	10/1000 μ s, Non-repetitive	10	A
		10/200 μ s, Non-repetitive	19	
Maximum Reverse Voltage	V _{RM}		23	V

●Electrical Characteristics (Tl=25℃)

Item	Symbol	Conditions	Ratings	Unit
Breakdown Voltage	V _{BR}	I _R = 1mA	24.3~29.7	V
Clamping Voltage	V _{CL}	I _{PP} = 10A	MAX 37	V
Reverse Current	I _R	V _R = 23V	MAX 5	μ A


ST04-27

Clamping Voltage




ST04-27


Breakdown Voltage



ST04-27


Reverse Current





ST04-27

Junction Capacitance



ST04-27

Junction Capacitance

