



FEATURES:

- This telephone plug is commonly used in switching panels and telecommunication equipment.
- Readily adapts telecommunication equipment for connection to BNC coaxial cables.
- Only the tip and ring are connected. The tip is connected to center contact and the ring is connected to the shell of the BNC. The sleeve is floating.

MATERIALS:

BNC: Outer shell is brass with tarnish resistant plating. Center contact is Beryllium Copper with gold plating.

Plug: Brass with black ABS insulation. Marking: "Model 2798"

RATINGS:

Operating Voltage: 500V (Disconnect power before handling)

Operating Temperature: +50°C (+122°F) Max.

ORDERING INFORMATION: Model 2798

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90308 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com