


Specifications:

Resonant Frequency (Hz)	3400 ± 500
Operating Voltage Max (Vdc)	3 ~ 28
Rated Voltage (Vdc)	9.0
Current Consumption Max. (mA)	12 at Rated Voltage
Sound Pressure Level Min. (dB)	105 at 10cm at Rated Voltage
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Housing	PC plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	12.0
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant


Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PT-3534FPQ](#)