

**Part Number: 88498-0030****Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-B Full-Rated, 1.50m Length***Image not available*

Status:	OBsolete
Replacement:	Contact Molex
Series:	88498
Category:	Cable Assemblies
Old Part Number:	88481-0140

*Series image - Reference only***Product Environmental Compliance**[EU RoHS](#): Compliance Status Not Reviewed[China RoHS](#):[REACH SVHC](#): Not Reviewed[Low-Halogen Status](#): Not Reviewed**Part Detail****General**

Status	Obsolete
Category	Cable Assemblies
Series	88498
Comments	Full-rated
Connector to Connector	USB Type A-to-B
Product Name	USB

Physical

Cable Length	1.50m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	None
Material - Resin	PVC
Packaging Type	Bag
Pitch - Mating Interface	2.00mm, 2.50mm
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Jacketed

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	1A
Shielded	Yes

Material Info

Old Part Number	88481-0140
-----------------	------------

Reference - Drawing Numbers

Product Specification	PS-88498-001
Sales Drawing	SD-88498-003

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)