


Straight Blade Devices

Heavy-Duty Specification Grade Receptacles

15 & 20A, 125 & 250V

Features

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors. Eight back wire holes.
- Auto-ground clip assures positive ground.



Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596	 C22.2 No. 42
Duplex Receptacles Back & Side Wire						
PS5262-I	15 125	Ivory	5-15R	•	•	•
PS5262-W	15 125	White	5-15R	•	•	•
PS5262	15 125	Brown	5-15R	•	•	•
PS5262-GRY	15 125	Gray	5-15R	•	•	•
PS5262-BK	15 125	Black	5-15R	•	•	•
PS5262-RED	15 125	Red	5-15R	•	•	•
PS5262-LA	15 125	Light Almond	5-15R	•	•	•
PS5262-BL	15 125	Blue	5-15R	•	•	•
PS5362-I	20 125	Ivory	5-20R	•	•	•
PS5362-W	20 125	White	5-20R	•	•	•
PS5362	20 125	Brown	5-20R	•	•	•
PS5362-GRY	20 125	Gray	5-20R	•	•	•
PS5362-BK	20 125	Black	5-20R	•	•	•
PS5362-RED	20 125	Red	5-20R	•	•	•
PS5362-LA	20 125	Light Almond	5-20R	•	•	•
PS5362-BL	20 125	Blue	5-20R	•	•	•
5662-I	15 250	Ivory	6-15R	•	•	•
5662-W	15 250	White	6-15R	•	•	•
5662	15 250	Brown	6-15R	•	•	•
5862-I	20 250	Ivory	6-20R	•	•	•
5862-W	20 250	White	6-20R	•	•	•
5862	20 250	Brown	6-20R	•	•	•
5862-GRY	20 250	Gray	6-20R	•	•	•
5862-BK	20 250	Black	6-20R	•	•	•
5862-RED	20 250	Red	6-20R	•	•	•

For Configurable Solutions, see Page U-1.

2 Pole, 3 Wire

NEMA
5-15RNEMA
5-20RNEMA
6-15RNEMA
6-20R