





NOTE: HARDWARE IS INCLUDED.

CAPACITANCE	5000 pF GMV
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMPS
WORKING VOLTAGE	85°C 200 VDC 125°C 100 VDC
DC RESISTANCE	.01 OHMS MAX.

IL=PER MIL-STD-220, NO LOAD

FREQ. MHz	I.L. (db)
10	20
50	
100	65
1 GHz	70
10 GHz	70


SCHEMATIC



CAPACITANCE

PART: S016
 BAG:
 1270-016
 DATE CODE
 QTY./BAG (200 MAX.)

SUGGESTED MOUNTING HOLE: $\phi.221$

	9	8	7	6	5	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api  FAIRVIEW PENNSYLVANIA technologies corp.	
	CN #22310	CN 58496-ENG	CN 211284	CN 200664	CN 184990 REDRAWN	CHANGE NOTICE	Fractions $\pm 1/64$ Dec. $.xx \pm$ Dec. $.xxx \pm .010$ Angles $\pm 0^\circ 30'$		
							CODE IDENT. NO. DLSP2	Dwn. KAUFFMAN Date 10-11-16	Description FILTER SING, PI, BSHG.
								Scale NONE	1270-016