

"F" CONNECTORS

Note: Unless otherwise stated, all items are Nickel Plated

CRIMP-TYPE "F" CONNECTOR

1/4" Crimping ring



Wire Type	Plating	Part No.
RG59/U	Tin	FC65
RG59/U	Gold	FC65G
RG59/U	Tin	FC65-50*
RG6/U	Tin	FC56
RG6/U	Tin	FC56-50*

*asterisk items are 50 piece display pack.

Crimp Rings

1/4" Rings for above Connectors.

For Connector	Crimp Ring	Part No.
No. FC65	No. R65B	
No. FC56	No. R56B	

Order rings in increments of 100, bulk packed.

CRIMP-TYPE "F" CONNECTOR

Attached Ring.

Wire Type	Part No.
RG59/U	FC65A
RG59/U	FC65A-50*
RG6/U	FC56A
RG6/U	FC56A-50*

* asterisk items are 50 piece display pack.

Weather Proof "F" Connector for RG6/U



One piece, High Quality "F" Connector. Brass and Cadmium Plated.

No. FCW6 - With rubber "O" ring

No. FCW6A - With rubber "O" ring and silicone gel for maximum protection against harsh environments.

DIRECT CRIMP "F" CONNECTOR

Fastest to install
F-connector with integral crimping ring.



Wire type	Part No.
RG59/U	FC79
RG6/U	FC79A
RG58/U	FC81
push-on for RG59	FC83

SOLDERLESS TWIST-ON "F" CONNECTORS



Wire type	Plating	Part No.
RG59/U	Gold Plated	FCG59C
RG6/U	nickel plated	FC59A
RG6/U	50-pack of above	FC59A-50
RG6/U	Gold Plated	FCG59A
RG59/U	Nickel plated	FC59C
RG59/U	50-pack of above	FC59C-50
RG59	for Belden 8281	FC59N
RG6/QUAD for quad shield		FC59Q

FOIL SHIELD CRIMP-ON "F" CONNECTORS

Suitable for all wires but a longer crimping ferrule is meant especially for cables with a foil type shield.



Wire Type	Part No.
RG59/U	FC57
RG6/U	FC57A
RG6 Teflon/Plenum	FC86
RG6/U Quad Shield	FC88
50-pack of FC57	FC57-50
50-pack of FC57A	FC57A-50
RG11/U	FC11

Foil Shield Crimp-On "F" Connectors



Wider Hex, for easy installations
Brass material, Nickel plated

Wire Type	Part No.
RG59/U	FCD57
RG6/U	FCD57A

Push-On

Male "F" for
RG59/U
with separate 1/4"
crimping ring.



No. FC80

"F"-Type GROUND BLOCK


In line ground with
females on each
end and ground connecting screw.



No. FC55

DUAL "F" GROUND BLOCK

for two lines,
females on
each end,
with mount-
ing screws.



No. FC25

TWIST-ON PUSH-ON "F" CONNECTOR

For RG59/U cable.



No. FC58A

Female "F" TERMINATOR

75 ohms; to eliminate
reflections.



No. FC2 - half watt terminator

10 Pack "F" CONNECTORS

Common crimp type and twist-on type "F" connectors for both RG59/U and RG6/U. Both are packaged in an attractive space saving blister card (2-7/8" x 3-3/4"). Blister cards are printed with a full description and clear terminating instructions on back of card.



Crimp Type
with attached ring



Twist-on type



Crimp type with
1/4" crimping ring



Weather proof



Crimp type
with attached ring



Female coupler

Part Number	Description	Wire Type	Part Number	Description	Wire Type
No. 48-800	Crimp type with 1/2" attached ring	RG59/U	No. 48-830	Crimp type - weather proof	RG6/U
No. 48-805	Crimp type with 1/2" attached ring	RG6/U	No. 48-825	Crimp type with attached crimping ring	RG59/U
No. 48-810	Twist-on type with long barrel	RG59/U	No. 48-855	Crimp type with attached crimping ring	RG6/U
No. 48-815	Twist-on type with long barrel	RG6/U	No. 48-840	Gold plated twist-on type	RG59/U
No. 48-820	Crimp type with 1/4" crimping ring	RG59/U	No. 48-845	Gold plated crimp type w 1/4" crimping ring	RG59/U
No. 48-850	Crimp type with 1/4" crimping ring	RG6/U	No. 48-860	"F" female coupler (F-81) with nut & washer	