

Products

Overview

Worm Gear and General Purpose

9/16" Worm Drive Clamps

1/2" Band Clamps

Small Diameter Clamps

Lined Clamps

Solid Clamps (Non-Perforated)

Spring Clamps

Heavy Duty Clamps

Specialty Clamps

No-Hub Couplings

Want a sales rep to contact you?

We'll help with any questions or set up an order for you.

[Click here to Contact Us](#)



Announcements

[NSF Certification on Standard Duty and Classic No-Hub Couplings](#) 04/19/2011

[more info](#)

search

[go](#)



We think about clamps . .
so you don't have to...

[Ideal Tridon](#) / [Catalog](#) / [Worm Gear and General Purpose](#) / [9/16" Worm Drive Clamps](#) / [IDEAL® 68 Series](#) /

General Purpose 9/16" Worm Gear

IDEAL® 68 Series

All stainless steel construction especially suited for industrial applications. With 5/16" hex head screw.



Material Specifications

Screw: 5/16" hex head. 410 stainless steel.

Band: 9/16" band width. 201/301 stainless steel.

Housing: 201/301 stainless steel.

[REQUEST QUOTE](#)

[contact us](#)

SIZING / CLAMPING RANGE CHART

SAE Sizes	Part No.	Min. Dia. (in.)	Max. Dia. (in.)	Min. Dia. (mm)	Max. Dia. (mm)	Fits Hose I.D. Min. (in.)	Fits Hose I.D. Max. (in.)
6	6806	3/8	7/8	10	22	5/16	3/8
8	6808	7/16	1	11	25	5/16	1/2
10	6810	1/2	1 1/16	13	27	3/8	5/8
12	6812	1/2	1 1/4	13	32	3/8	3/4
16	6816	11/16	1 1/2	18	38	3/4	7/8
20	6820	3/4	1 3/4	19	44	3/4	1 1/8
24	6824	1	2	25	51	7/8	1 3/8
28	6828	1 1/4	2 1/4	32	57	1 1/4	1 5/8
32	6832	1 1/2	2 1/2	38	63	1 1/2	1 7/8
36	6836	1 3/4	2 3/4	44	70	1 3/4	2
40	6840	2	3	51	76	2	2 1/4
44	6844	2 1/4	3 1/4	57	82	2 1/4	2 1/2
48	6848	2 1/2	3 1/2	64	89	2 1/4	2 3/4
52	6852	2 3/4	3 3/4	70	95	2 3/4	3
56	6856	3	4	76	101	3	3 1/2
60	6860	3 1/4	4 1/4	83	108	3 1/4	3 3/4
64	6864	2 1/2	4 1/2	64	114	2 1/2	4
72	6872	3	5	76	127	3	4 1/2
80	6880	3 1/2	5 1/2	89	140	3 1/2	5
88	6888	4	6	102	152	4	5 1/2
96	6896	4 1/2	6 1/2	114	165	4 1/2	6
104	68104	5	7	127	178	5	6 1/2

[REQUEST QUOTE](#)