

Base Mount Terminal Blocks

MAGNUM[®]

GET CONNECTED WITH US

KT3

Inches (Millimeters)

SPECIFICATIONS

Rating: 40A, 600V; UL/CSA

Center spacing: .390" (9.91)

Number of poles: 3

Circuits per foot: 28

Circuit jumper: JN3, 2 circuits

Wire size: #8-22 CU

Screw size: #8-32

Mounting options: Base Mount,
Stackable

Marking tape: MT12-1/2

Torque rating: 18 in/lb max.

Operating temperature: 105°C



KAD

End Mount Adapter Optional

