





2-Piece Fixing Ties with Pipe Clip, twistable 360°

Features and Benefits


This simple to use inside serrated tie provides the opportunity to attach an additional 5mm diameter cable, pipe or hose to an existing bundle. Offering the facility of a full 360 degrees of rotation, the second bundle can be orientated in any direction in relation to the main harness. Ideally suited for any application where the cable, pipe or hose can move in relation to the fixing point.



T50SVC65



T50SVC5



T50SVC5 rotates in any direction.

Material Data

Cable Tie	Polyamide 6.6 Heat Stabilised (PA66HS)
Operating Temperature	-40 °C to +105 °C Continuous, (+145 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Attach to Ø	Material	Colour
156-00318	T50SVC4S	155	4,7	35.0	225	3.8-4.2	PA66HS, PP	Black (BK), Natural (NA)
156-00447	T50SVC4	155	4.7	35.0	225	3.8-4.2	PA66HS, PA66HIRHS	Black (BK)
155-31202	T50SVC5	155	4.7	35.0	225	4.5-5.2	PA66HS	Black (BK)
156-00155	T50SVC65	155	4.7	35.0	225	6.5-8.0	PA66HS, PA66HIRHS	Black (BK)
156-00134	T50SVCOC10-14	155	4.7	35.0	225	10.0-14.0	PA66HS, PA66HIRHS	Black (BK)
156-00135	T50SVCOC15-18	155	4.7	35.0	225	15.0-18.0	PA66HS, PA66HIRHS	Black (BK)
156-00136	T50SVCOC19-24S	155	4.7	35.0	225	19.0-24.5	PA66HS, PA66HIRHS	Black (BK)
156-00272	T50SVCOC25-31	155	4.7	35.0	225	25.0-31.0	PA66HS, PA66HIRHS	Black (BK)
156-00273	T50SVCOC31-39	155	4.7	35.0	225	31.0-39.0	PA66HS, PA66HIRHS	Black (BK)
156-00137	T50SVCOC39-45	155	4.7	35.0	225	39.0-45.0	PA66HS, PA66HIRHS	Black (BK)
156-00128	T50SMVCOC10-14	210	4.7	50.0	225	10.0-14.0	PA66HS, PA66HIRHS	Black (BK)
156-00129	T50SMVCOC15-18SET	210	4.7	50.0	225	15.0-18.0	PA66HS, PA66HIRHS	Black (BK)
156-00130	T50SMVCOC19-24S	210	4.7	50.0	225	19.0-24.5	PA66HS, PA66HIRHS	Black (BK)
156-00577	T50SMVCOC1924S	210	4.7	50.0	225	19.0-24.5	PA46	Grey (GY)
156-00303	T50SMVCOC25-31	210	4.7	50.0	225	25.0-31.0	PA66HS, PA66HIRHS	Black (BK)
156-00304	T50SMVCOC31-39	210	4.7	50.0	225	31.0-39.0	PA66HS, PA66HIRHS	Black (BK)
156-00131	T50SMVCOC39-45SET	210	4.7	50.0	225	39.0-45.0	PA66HS, PA66HIRHS	Black (BK)

All dimensions in mm. Subject to technical changes.