



## FEATURES:

- Shielded cable to reduce noise
- WE-310 and Bantam Plugs molded to the cable for optimum durability
- Available in three lengths

## MATERIALS:

Plugs – (4280) Brass, unplated

(4280N) Brass, nickel plated

Cable – 2 Conductor shielded twisted pair, PVC jacket and insulation

## RATINGS:

Operating Voltage: 300 VRMS Max.

Operating Temperature: +50°C to (+122°F) Max.

Current: 3.36 Amperes @ 25°C

Nominal Capacitance Shield Conductors: 720pf

Nominal Capacitance Between Conductors: 420pf

## ORDERING INFORMATION: Model 4280 or 4280N-XX

XX = Length in inches

Standard Lengths 36" (914 mm), 48" (1219 mm), 60" (1520 mm)

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4280-48](#)