



In professional hands
since 1886.

Quality for work Value for money




Extended range with proven performance and reliability


Tools made of high grade Chrome-Vanadium steel for strength and tolerance. Small, flat heads and Dynamic Drive profile designed for easy access in confined spaces.

All tools are attached to an informative plastic card supplied with a hanging hole. This makes the tools easy to display and facilitates the purchase for the customer.

Combination spanners



Double open end spanners



Product code	EAN 731415+				a1 x a2 mm	b1 x b2 mm	
SBS20-6	3009104	1	6	105	5.0x3.9	10.0x14.5	13
SBS20-7	3009111	1	7	110	5.6x4.1	11.0x17.0	18
SBS20-8	3009128	1	8	110	5.6x4.2	12.5x18.0	18
SBS20-9	3009135	1	9	120	6.0x4.5	14.0x21.0	22
SBS20-10	3009142	1	10	135	6.6x5.0	15.5x22.5	30
SBS20-11	3009159	1	11	135	6.6x5.0	17.0x23.5	30
SBS20-12	3009166	1	12	150	7.5x5.5	18.5x26.5	45
SBS20-13	3009173	1	13	160	7.5x5.7	20.0x28.5	45
SBS20-14	3009180	1	14	168	8.2x6.4	21.5x31.5	65
SBS20-15	3009197	1	15	170	8.2x6.4	22.5x33.0	65
SBS20-16	3009203	1	16	178	8.8x6.7	24.0x34.5	80
SBS20-17	3009210	1	17	190	9.5x7.1	25.5x37.5	110
SBS20-18	3009227	1	18	210	10.0x7.5	27.0x39.0	115
SBS20-19	3009234	1	19	220	10.0x7.5	28.0x41.0	120
SBS20-20	3009241	1	20	232	11.0x8.1	29.5x43.0	150
SBS20-21	3009258	1	21	250	11.0x8.1	31.5x44.5	150
SBS20-22	3009265	1	22	255	12.0x8.9	34.8x49.0	200
SBS20-24	3009272	1	24	280	13.0x9.2	36.0x50.5	265
SBS20-27	3009289	1	27	310	14.0x9.8	40.0x57.0	350
SBS20-30	3009296	1	30	355	15.0x10.8	43.5x62.5	480
SBS20-32	3009302	1	32	360	15.0x10.8	48.5x65.5	500
SBS20-1/4	3012296	1	1/4	105	3.9x5.0	10.0x14.5	12
SBS20-5/16	3012302	1	5/16	110	4.2x5.6	12.5x18.0	18
SBS20-3/8	3012319	1	3/8	120	4.5x6.0	14.0x21.0	25
SBS20-7/16	3012326	1	7/16	140	5.0x6.6	17.0x23.5	30
SBS20-1/2	3012333	1	1/2	160	5.7x7.5	20.0x28.5	50
SBS20-9/16	3012340	1	9/16	165	6.4x8.2	21.5x31.5	65
SBS20-5/8	3012357	1	5/8	180	6.7x8.8	24.0x34.5	75
SBS20-11/16	3012364	1	11/16	195	7.1x9.5	25.5x37.5	85
SBS20-3/4	3012371	1	3/4	220	7.5x10.0	28.0x41.0	120
SBS20-13/16	3012388	1	13/16	250	8.1x11.0	31.5x44.5	165
SBS20-7/8	3012395	1	7/8	260	8.9x12.0	34.5x49.0	210
SBS20-15/16	3012401	1	15/16	280	9.2x13.0	36.0x50.5	260
SBS20-1	3012418	1	1	260	9.2x13.0	37.5x52.0	260
SBS20-1.1/16	3012425	1	1.1/16	350	9.8x14.0	40.0x57.0	350
SBS20-1.1/8	3012432	1	1.1/8	310	9.8x14.0	42.0x58.5	390
SBS20-1.1/4	3012449	1	1.1/4	360	10.8x15.0	48.5x65.5	480
SBS20-1.5/16	3012456	1	1.5/16	375	10.8x15.0	49.0x65.0	500

Product code	EAN 731415+				a mm	b1 mm	b2 mm	
SBS10-6-7	3009005	1	6 x 7	122	3.4	16.5	18.5	21
SBS10-8-9	3010650	1	8 x 9	140	3.7	21.0	22.5	31
SBS10-10-11	3009012	1	10 x 11	157	4.0	24.0	28.0	46
SBS10-12-13	3009029	1	12 x 13	172	4.5	28.5	31.5	59
SBS10-14-15	3009036	1	14 x 15	190	4.8	32.5	35.0	83
SBS10-16-17	3009043	1	16 x 17	205	5.5	36.5	39.0	125
SBS10-17-19	3010667	1	17 x 19	222	5.8	40.5	43.0	152
SBS10-18-19	3009050	1	18 x 19	222	5.8	41.0	43.0	159
SBS10-20-22	3009067	1	20 x 22	236	6.3	45.0	48.5	198
SBS10-21-23	3009074	1	21 x 23	245	6.8	46.5	50.5	230
SBS10-24-27	3009081	1	24 x 27	275	8.0	55.0	58.0	360
SBS10-30-32	3009098	1	30 x 32	300	8.6	64.0	68.5	440
SBS10-1/4-5/16	3012227	1	1/4-5/16	130	3.4	17.0	20.0	21
SBS10-3/8-7/16	3012234	1	3/8-7/16	157	4.0	24.0	28.0	46
SBS10-1/2-9/16	3012241	1	1/2-9/16	180	4.5	30.0	34.0	82
SBS10-5/8-11/16	3012258	1	5/8-11/16	205	5.8	39.0	43.0	156
SBS10-3/4-7/8	3012265	1	3/4-7/8	236	6.3	42.0	48.0	190
SBS10-13/16-7/8	3012272	1	13/16-7/8	245	6.8	45.0	50.0	235
SBS10-15/16-1	3012289	1	15/16-1	266	7.4	52.0	55.0	280



Sets of Combination spanners in plastic holder

Product code	EAN 731415+			Width mm	
S20/SH6	3013316	1	6	8, 10, 12, 13, 14, 17	388
S20/SH12	3013378	1	12	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19	1050
BS20/S10	3009319	1	10	8, 10, 11, 13, 14, 16, 17, 18, 19, 22	1205


In attractive sales card board box

Sets of Double open-end spanners in plastic holder

Product code	EAN 731415+			Width mm	
S10/SH6	3013309	1	6	8-9, 10-11, 12-13, 14-15, 16-17, 18-19	553
S10/SH11	3013408	1	11	6-7, 8-9, 10-11, 12-13, 14-15, 16-17, 17-19, 18-19, 20-22, 21-23, 24-27	1604




Flex-head spanner



Product code	EAN 731415+				a1 x a2 mm	b1 x b2 mm	
SBS50-8-9	3009326	1	8 x 9	168	9.1	10.3	77
SBS50-10-11	3009333	1	10 x 11	199	14.1	15.3	87
SBS50-12-13	3009340	1	12 x 13	224	16.6	17.8	160
SBS50-14-15	3009357	1	14 x 15	249	19.1	20.3	198
SBS50-16-17	3009364	1	16 x 17	253	21.6	22.8	209
SBS50-18-19	3009371	1	18 x 19	303	24.2	25.3	393
SBS50-20-22	3009388	1	20 x 22	305	26.6	29.1	403
SBS50-21-23	3009395	1	21 x 23	306	27.8	30.5	490

Double ended box spanners, deep offset



Product code	EAN 731415+				a1 x a2 mm	b1 x b2 mm	
SBS30-6-7	3009425	1	6 x 7	168	5.4x5.9	10.5x12.2	40
SBS30-8-9	3009432	1	8 x 9	180	6.4x7.9	13.2x14.8	55
SBS30-10-11	3009449	1	10 x 11	195	7.2x7.9	16.0x17.4	85
SBS30-12-13	3009456	1	12 x 13	220	8.3x9.1	18.8x20.0	125
SBS30-14-15	3009463	1	14 x 15	230	9.1x9.9	21.8x23.0	155
SBS30-16-17	3009470	1	16 x 17	245	10.2x11.0	24.5x26.0	200
SBS30-17-19	3010674	1	17 x 19	270	11.0x11.8	26.0x27.8	255
SBS30-18-19	3009487	1	18 x 19	275	11.0x11.8	28.0x29.0	260
SBS30-20-22	3009494	1	20 x 22	300	12.3x12.8	30.6x33.0	350
SBS30-21-23	3009500	1	21 x 23	310	12.4x13.3	31.4x35.4	390
SBS30-24-27	3009517	1	24 x 27	340	14.3x15.2	36.0x40.2	530
SBS30-30-32	3009524	1	30 x 32	650	16.2x16.7	44.5x47.0	650
SBS30-1/4-5/16	3012463	1	1/4-5/16	168	5.4x5.9	10.5x12.2	46
SBS30-3/8-7/16	3012470	1	3/8-7/16	195	7.2x7.9	16.0x17.4	80
SBS30-1/2-9/16	3012487	1	1/2-9/16	220	8.7x9.5	20.0x21.8	135
SBS30-5/8-11/16	3012494	1	5/8-11/16	245	10.2x11.0	24.5x22.5	200
SBS30-3/4-7/8	3012500	1	3/4-7/8	300	11.8x12.8	29.0x33.0	330
SBS30-15/16-1	3012517	1	15/16-1	330	13.6x14.3	35.7x38.5	470
SBS30-1.1/4-1.5/16	3012524	1	1 1/4-1 5/16	400	17.8x19.2	48.0x54.0	660



Set in plastic wallet

Product code	EAN 731415+			Width mm	
BS50/6T	3009418	1	6	8x9, 10x11, 12x13, 14x15, 16x17, 18x19	1220

More complete than ever, now including 3/8" drive assortment

1/4"

All sockets are featuring the Dynamic Drive profile, for higher efficiency and an optimal grip without damaging the bolts and nuts.

Sliding T-handle, 1/4"

Product code	EAN 731415+				
SBS64	3012609	1	125	40	

Adaptor, 1/4"

Product code	EAN 731415+				
SBS69	3009722	1	1/4"	3/8"	25 25

Universal joint, 1/4"

Product code	EAN 731415+				
SBS65	3009715	1	32.5	18	

Extension bars, 1/4"

Product code	EAN 731415+				
SBS63-2	3009685	1	50	23	
SBS63-4	3009692	1	100	45	
SBS63-6	3009708	1	150	65	

Reversible ratchet, 1/4"

Product code	EAN 731415+				
SBS61	3009661	1	130	95	

Breaker bar, 1/4"

Product code	EAN 731415+				
SBS67	3009678	1	153	95	

Hexagon sockets, 1/4"

Product code	EAN 731415+				D1 mm	D2 mm	
SBS60-4	3009531	1	4	25.0	6.7	12.1	9
SBS60-4.5	3009548	1	4.5	25.0	7.2	12.1	10
SBS60-5	3009555	1	5	25.0	7.7	12.1	10
SBS60-5.5	3009562	1	5.5	25.0	8.3	12.1	10
SBS60-6	3009579	1	6	25.0	9.3	12.1	10
SBS60-7	3009586	1	7	25.0	10.5	12.1	12
SBS60-8	3009593	1	8	25.0	11.5	12.1	12
SBS60-9	3009609	1	9	25.0	12.7	12.1	12
SBS60-10	3009616	1	10	25.0	14.0	12.1	15
SBS60-11	3009623	1	11	25.0	15.4	13.1	18
SBS60-12	3009630	1	12	25.0	16.5	14.0	18
SBS60-13	3009647	1	13	25.0	17.6	15.0	20
SBS60-14	3009654	1	14	25.0	18.8	16.0	22
SBS60-3/16	3012579	1	3/16	22.2	7.7	12.1	10
SBS60-1/4	3012548	1	1/4	22.2	9.3	12.1	11
SBS60-5/16	3012555	1	5/16	22.2	11.5	12.1	12
SBS60-11/32	3012562	1	11/32	22.2	12.6	12.1	13
SBS60-3/8	3012531	1	3/8	22.2	13.7	12.1	16
SBS60-7/16	3012586	1	7/16	22.2	15.4	13.0	16
SBS60-1/2	3012593	1	1/2	22.2	17.5	15.0	23

The S-line assortment has now been extended with both inch sizes and a complete 3/8" assortment. All to fulfil customer requirements.

Reversible ratchet, 3/8"

Product code	EAN 731415+				
SBS750	3012883	1	200	235	

Extension bars, 3/8"

Product code	EAN 731415+				
SBS760	3012937	1	75	80	
SBS761	3012944	1	125	115	
SBS762	3012951	1	250	210	

Sliding T-handle, 3/8"

Product code	EAN 731415+				
SBS755	3012913	1	160	130	

Universal joint, 3/8"

Product code	EAN 731415+				
SBS775	3012920	1	52	70	

Breaker bar, 3/8"

Product code	EAN 731415+				
SBS705	3012968	1	240	250	

Adaptors, 3/8"

Product code	EAN 731415+					
SBS723	3012890	1	3/8"	1/4"	27	25
SBS724	3012906	1	3/8"	1/2"	35	62

Hexagon sockets, 3/8"

Product code	EAN 731415+				D1 mm	D2 mm	
SBSF-6	3012616	1	6	25.9	10.0	17.3	15
SBSF-7	3012623	1	7	25.8	10.5	17.3	15
SBSF-8	3012630	1	8	25.8	11.4	17.3	16
SBSF-9	3012647	1	9	25.8	12.8	17.3	19
SBSF-10	3012654	1	10	25.8	14.3	17.3	19
SBSF-11	3012661	1	11	25.8	15.7	17.3	20
SBSF-12	3012678	1	12	25.8	16.6	17.3	22
SBSF-13	3012685	1	13	25.8	18.0	17.3	22
SBSF-14	3012692	1	14	26.2	19.6	18.0	23
SBSF-15	3012708	1	15	27.8	20.4	19.0	25
SBSF-16	3012715	1	16	28.3	21.1	20.0	25
SBSF-17	3012722	1	17	28.8	22.8	20.0	30
SBSF-18	3012739	1	18	29.5	24.3	21.0	30
SBSF-19	3012746	1	19	30.1	25.1	22.0	40
SBSF-1/4	3012753	1	1/4	25.8	10.0	17.3	24
SBSF-5/16	3012760	1	5/16	25.8	10.0	17.3	24
SBSF-3/8	3012777	1	3/8	25.8	14.3	17.3	24
SBSF-7/16	3012784	1	7/16	25.8	15.7	17.3	25
SBSF-1/2	3012791	1	1/2	25.8	18.0	17.3	27
SBSF-17/32	3012807	1	17/32	25.8	18.0	17.3	27
SBSF-9/16	3012814	1	9/16	27.4	19.6	17.3	28
SBSF-19/32	3012821	1	19/32	28.3	21.1	19.0	34
SBSF-5/8	3012838	1	5/8	28.3	21.1	19.0	34
SBSF-11/16	3012845	1	11/16	28.8	23.6	20.5	34
SBSF-3/4	3012852	1	3/4	30.2	25.2	22.0	52
SBSF-13/16	3012869	1	13/16	31.3	26.7	24.0	63
SBSF-7/8	3012876	1	7/8	32.5	29.1	26.0	78

Versatile 1/2" drive assortment for your toughest jobs

The S-line assortment provides superior reliability, flexibility and ease of use.



Reversible ratchet, 1/2"

Product code	EAN 731415+			
SBS81	3009937	1	270	575
SBS82	3009944	1	270	470



Universal joint, 1/2"

Product code	EAN 731415+			
SBS85	3010025	1	72	160



Hexagon sockets, 1/2"

Product code	EAN 731415+				D1 mm	D2 mm	
SBS80-8	3013194	1	8	38	12.9	22.0	42
SBS80-9	3013200	1	9	38	14.2	22.0	42
SBS80-10	3009746	1	10	38	15.4	22.0	51
SBS80-11	3009753	1	11	38	16.6	22.0	51
SBS80-12	3009760	1	12	38	17.9	22.0	51
SBS80-13	3009777	1	13	38	19.1	22.0	53
SBS80-14	3009784	1	14	38	20.4	22.0	54
SBS80-15	3009791	1	15	38	21.6	22.0	64
SBS80-16	3009807	1	16	38	22.9	22.0	64
SBS80-17	3009814	1	17	38	24.1	23.0	72
SBS80-18	3009821	1	18	38	25.4	23.5	76
SBS80-19	3009838	1	19	38	26.6	24.0	80
SBS80-21	3009852	1	21	39	29.1	25.0	102
SBS80-22	3010117	1	22	38	30.4	25.5	109
SBS80-23	3009869	1	23	40	31.6	26.0	109
SBS80-24	3009876	1	24	41	32.9	26.5	121
SBS80-27	3009883	1	27	44	36.6	29.0	173
SBS80-30	3009890	1	30	47	40.4	29.5	189
SBS80-32	3009906	1	32	47	42.9	30.5	227
SBS80-1/4	3012975	1	1/4	38	10.3	22.0	40
SBS80-5/16	3012982	1	5/16	38	12.9	22.0	40
SBS80-3/8	3012999	1	3/8	38	15.4	22.0	44
SBS80-7/16	3013002	1	7/16	38	16.6	22.0	44
SBS80-1/2	3013019	1	1/2	38	18.8	22.0	50
SBS80-9/16	3013026	1	9/16	38	20.8	22.0	51
SBS80-5/8	3013033	1	5/8	38	22.8	22.8	55
SBS80-11/16	3013040	1	11/16	38	24.7	24.7	67
SBS80-3/4	3013057	1	3/4	38	26.6	24.0	79
SBS80-13/16	3013064	1	13/16	40	29.1	25.0	99
SBS80-7/8	3013071	1	7/8	40	30.6	26.0	116
SBS80-15/16	3013088	1	15/16	42	32.7	27.0	128
SBS80-1	3013095	1	1	42	34.1	27.0	132
SBS80-1.1/16	3013101	1	1 1/16	46	39.0	29.0	146
SBS80-1.1/8	3013118	1	1 1/8	46	39.0	29.0	146
SBS80-1.3/16	3013125	1	1 3/16	48	40.6	33.0	192
SBS80-1.1/4	3013132	1	1 1/4	49	42.9	35.0	186
SBS80-1.5/16	3013149	1	1 5/16	49	44.5	36.0	207

Adaptors, 1/2"

Product code	EAN 731415+				
SBS88	3010001	1	1/2"	37	70
SBS89	3010018	1	1/2"	45	140



Breaker bar, 1/2"

Product code	EAN 731415+			
SBS87S	3009951	1	257	450
SBS87	3009968	1	390	610



Socket sets on holder, 1/2"

Product code	EAN 731415+		Size mm		
BS80/6	3013163	1	10, 13, 16, 17, 19, 24	235x75x33	365
S80/8	3013170	1	10, 12, 13, 16, 17, 18, 19, 24	315x75x34	402
S80/17	3013187	1	10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27, 30, 32 & S82	180x165x60	1380



Sliding T-handle, 1/2"

Product code	EAN 731415+			
SBS86	3009999	1	300	445

Extension bars, 1/2"

Product code	EAN 731415+			
SBS83-3	3013156	1	75	126
SBS83-5	3009975	1	125	120
SBS83-10	3009982	1	250	365

Sparkplug sockets, 1/2"

Product code	EAN 731415+				D1 mm	D2 mm	
SBS80S-16	3009913	1	16	5/8	69	21.8	100
SBS80S-21	3009920	1	21	13/16	73	28.3	173

Two component handle for comfort and strength

All ratchets, breaker bars and spinner handles feature a two component handle combining a warm, comfortable grip with excellent resistance to repeated high impact. The handle is also resistant to aggressive solvents.

Please note! The new two-component handle and push button for safe and quick socket changes, are available from the beginning of 2006.



Socket sets in sturdy, stackable cases in new innovative design

These sets are available in 10 different sizes to fulfil most demands. The range includes small basic sets as well as large combined socket and spanner sets.

All tools are made of Chrome-Vanadium steel and conform to the ISO/DIN standards. These tools help to make tough jobs easy, and ensure that they are always close at hand.

The socket sets brand new design is lightweight, handy, and also heavy duty.



S160

Product code	EAN 731415+	Contents pcs			DIN/ISO
S160	0104031	16	280x160x70	1/4"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive profile, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Extension bar, 1 pce 1/4" Flexible extension bar, 1 pce 1/4" Reversible ratchet 60 teeth

S290

Product code	EAN 731415+	Contents pcs			DIN/ISO
S290	3000859	29	280x160x70	1/4"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive profile, 3 pcs 1/4" Socket drivers Slotted, 3 pcs 1/4" Socket drivers Phillips, 5 pcs 1/4" Socket drivers Hex, 2 pcs 1/4" Extension bar, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Universal joint, 1 pce 1/4" Spinner handle, 1 pce 1/4" Reversible ratchet 60 teeth



S460

Product code	EAN 731415+	Contents pcs			DIN/ISO
S460	0111060	46	375x215x100	1/4"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive profile, 3 pcs 1/4" Socket drivers Slotted, 4 pcs 1/4" Socket drivers Phillips, 6 pcs 1/4" Socket drivers Hex, 7 pcs 1/4" Socket drivers Torx, 3 pcs 1/4" Sockets Torx, 1 pce 1/4" Spinner Disc, 2 pcs 1/4" Extension bar, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Universal joint, 1 pce 1/4" Spinner handle, 1 pce 1/4" Flexible extension bar, 3 pcs L-Keys Hex, 1 pce 1/4" Reversible ratchet 60 teeth



All ratchet handles in the sets have comfortable two-component handles and are featuring 60-teeth/6° action. This provides good access in confined spaces.

Detachable combination spanner sets assures the convinience to have the correct size for the job at hand. All cases feature a unique locking device which is automatically disengages from the lid when opening.



S330

Product code	EAN 731415+	Contents pcs			DIN/ISO
S330	0104024	34	280x160x70	1/4", 3/8"	3120/1174

12 pcs 3/8" 6-pt Sockets Dynamic Drive profile, 2 pcs 3/8" Extension bars, 1 pce 3/8" Universal joint, 1 pce 3/8" x 1/4" Bit holder, 2 pcs 3/8" Spark Plug Sockets 6-pt, 1 pce 1/4" Spinner handle, 1 pce 1/4" x 1/4" Bit holder, 3 pcs 1/4" Bits Slotted, 4 pcs 1/4" Bits Phillips PH, 6 pcs 1/4" Bits Hex, 1 pce 3/8" Reversible ratchet 60 teeth



S240

Product code	EAN 731415+	Contents pcs			DIN/ISO
S240	0104017	24	375x215x100	1/2"	3120/1174

18 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" T-adaptor, 1 pce 1/2" Breaker bar, 1 pce 1/2" Reversible ratchet 60 teeth



S240AF

Product code	EAN 731415+	Contents pcs			DIN/ISO
S240AF	0111077	23	375x215x100	1/2"	3120/1174

15 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" T-adaptor, 2 pcs 1/2" Spark Plug Sockets 6-pt, 1 pce 1/2" Breaker bar, 1 pce 1/2" Reversible ratchet 60 teeth

Case close-ups

The new generation of Bahco socket sets are organized in convenient cases in a new contemporary design. All cases are stackable, made of sturdy shockproof High Density Polythene (HDPE) and equipped with locks and hinges for heavy-duty use.

Divider separates tool storage and can be detached for use as a comfortable kneepad.

A convenient removable three section plastic box with closable lid. For storing bolts, nuts, spare parts etc.

Durable two component handle in new design makes the case easy to grip and comfortable to carry.

Robust and easy to handle all-metal locking device. Spring-loaded mechanism disengages the lid fully.

Detachable spanner rack. Allowing you to take just the spanner set to your work.

The new strong hinge construction makes the case more durable.

S400

S400

Product code	EAN 731415+	Contents pcs			DIN/ISO
S400	0111053	40	375x320x110	1/2"	3120/1174

21 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" T-adapter, 1 pce 1/2" Breaker bar, 1 pce 1/2" Reversible ratchet 60 teeth, 13 pcs Comb. spanners

S910

S910

Product code	EAN 731415+	Contents pcs			DIN/ISO
S910	0104000	92	375x320x110	1/4", 1/2"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive, 10 pcs 1/4" 6-pt Deep Sockets Dynamic Drive profile, 13 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 2 pcs 1/4" Extension bars, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Universal joint, 1 pce 1/4" Bit holder, 1 pce 1/4" Bit adapter, 1 pce 1/4" Spinner handle, 1 pce 1/4" Magnetic adapter, 3 pcs 1/4" Bits Slotted, 5 pcs 1/4" Bits Phillips PH, 3 pcs 1/4" Bits Pozidriv PZ, 6 pcs 1/4" Bits Hex, 8 pcs 1/4" Bits TORX, 3 pcs 5/16" Bits TORX, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" Spark Plug Socket 6-pt, 1 pce 1/2" x 5/16" Bit holder, 1 pce 1/2" T-adapter, 3 pcs L-keys Hex, 1 pce 1/4" Reversible ratchet 60 teeth, 1 pce 1/2" Reversible ratchet 60 teeth, 4 pcs Flex head spanners, 6 pcs Comb. spanners

S106

Product code	EAN 731415+	Contents pcs			DIN/ISO
S106	0103997	106	375x430x110	1/4", 1/2"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive profile, 10 pcs 1/4" 6-pt Deep Sockets Dynamic Drive profile, 15 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 9 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 4 pcs 1/2" 6-pt Impact sockets, 3 pcs 1/4" Socket drivers Slotted, 4 pcs 1/4" Socket drivers Phillips PH, 3 pcs 1/4" Socket drivers Pozidriv PZ, 6 pcs 1/4" Socket drivers Hex, 8 pcs 1/4" Socket drivers TORX, 2 pcs 1/4" Extension bars, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Universal joint, 1 pce 1/4" Spinner handle, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" Spark Plug Socket 6-pt, 1 pce 1/2" T-adapter, 3 pcs L-Keys Hex, 1 pce 1/4" Reversible ratchet 60 teeth, 1 pce 1/2" Reversible ratchet 60 teeth, 4 pcs Flex head spanners, 13 pcs Comb. spanners

S87+7

Product code	EAN 731415+	Contents pcs			DIN/ISO
S87+7	0103980	94	375x430x110	1/4", 1/2"	3120/1174

12 pcs 1/4" 6-pt Sockets Dynamic Drive profile, 9 pcs 1/4" 6-pt Deep Sockets Dynamic Drive profile, 15 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 9 pcs 1/2" 6-pt Sockets Dynamic Drive profile, 4 pcs 1/2" 6-pt Impact sockets, 3 pcs 1/4" Socket drivers Slotted, 4 pcs 1/4" Socket drivers Phillips PH, 6 pcs 1/4" Socket drivers Hex, 2 pcs 1/4" Extension bars, 1 pce 1/4" Sliding T-bar, 1 pce 1/4" Universal joint, 1 pce 1/4" Spinner handle, 2 pcs 1/2" Extension bars, 1 pce 1/2" Universal joint, 1 pce 1/2" Spark Plug Socket 6-pt, 1 pce 1/2" T-adapter, 3 pcs L-Keys Hex, 1 pce 1/4" Reversible ratchet 60 teeth, 1 pce 1/2" Reversible ratchet 60 teeth, 4 pcs Flex head spanners, 13 pcs Comb. spanners

S106

S87+7

The right product information visible on the packaging.

All spanners, sockets, ratchets and accessories in the new Bahco range are on a new practical SB-packaging. This makes them easy to handle and to display on the wall, allowing you to look more closely at their design and finish. Each package is also supplied with clear, straightforward information about size and area of application. For the professional user, the package also carries all essential data, such as handle profile and gripping ability. The information is displayed in the form of easy to understand symbols, drawings and dimensions, designed to make your buying decision as easy as possible.

